








—SEE DETAIL B



DETAIL B
SCALE 16:1





SECTION A-A
SCALE 20:1

	1	2	3	4	5	6	7	8
i	C	C	C	S	S	S	S	C
h	C	C	C	S	S	S	S	S
g	C	C	C	S	S	S	S	S
f	C	C	C	S	S	S	S	S
e	C	C	C	S	S	S	S	S
d	C	C	C	S	S	S	S	S
c	C	C	C	S	S	S	S	S
b	C	C	C	S	S	S	S	S
a	C	C	C	S	S	S	S	C

S = SOLDER TAIL
C = COMPLIANT PIN

- △ HOUSING: LCP, UL94V0, COLOR: BLACK.
CONTACT: PHOSPHOR BRONZE.
- △ FINISH CONTACT: 1.27 μ m GOLD IN CONTACT AREA.
COMPLIANT PIN: 1.27 μ m MIN TIN-LEAD (93/7) ON PCB TAIL
OVER 2.54 μ m MIN. NICKEL OVER ALL.
SOLDER TAIL: 5.08 μ m MIN TIN-LEAD (93/7) ON PCB TAIL
OVER 2.54 μ m MIN. NICKEL OVER ALL.
- △ PLATED THROUGH HOLE PER 114-163004, FIGURE 10
- △ DATUMS AND BASIC DIMENSIONS ESTABLISHED
BY CUSTOMER.
- △ FINISH CONTACT: 1.27 μ m GOLD IN CONTACT AREA.
COMPLIANT PIN: 1.27 μ m MIN TIN ON PCB TAIL OVER
2.54 μ m MIN. NICKEL OVER ALL.
SOLDER TAIL: 5.08 μ m MIN TIN ON PCB TAIL
OVER 2.54 μ m MIN. NICKEL OVER ALL.

	2374807-2
	2374807-1
CONTACT PLATING	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. BELACK 11JUN2020 CHK D. HOANG 11JUN2020 APVD D. HOANG 11JUN2020		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.° 1 PLC ±0.5 2 PLC ±0.13 3 PLC ±.° 4 PLC ±.° ANGLES ±10°		NAME CONNECTOR ASSEMBLY, BACKPLANE VERTICAL RECEPTACLE, HALF, LEFT END, 20.3mm, MULTIGIG RT 3; SOLDER TAIL	
MATERIAL 		WEIGHT 3.55g		SIZE A100779	
		CUSTOMER DRAWING		DRAWING NO C=2374807	
				RESTRICTED TO -	
				SCALE 2:1 SHEET 1 OF 1 REV A	