


REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	M1	ECR-24-225217	06JAN2025	LP DSC



- 1 STAMP AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPEC SAE AS7928
COMMERCIAL WIRE RANGE IS 22-16.
- 2 WIRE INSUL DIA, $\phi 2.667 - 3.556$ [$\phi .105 - .140$].
- 3 BODY MATL THK, 0.787 ± 0.051 [$.031 \pm .002$].
- 4 BODY, NICKEL-PLATE PER SAE AMS QQ-N-290.
 0.076 [$.000300$] MIN EXT THK.
- 5 NOTE DELETED
- 6 MATERIAL: BODY - CU PER ASTM B152
SLEEVE - NI SILVER PER ASTM B122.
- 7 NOTE DELETED
- 8 NOTE DELETED
- 9 APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF
STUD HOLE

1000	LOOSE PIECE	322363
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 343°C [649°F]	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L OLMEDA 100CT94	TE Connectivity			
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: -	DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK M ELLIS 100CT94				NAME
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 0.26-1.65mm² [509-3260] STRANDED		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± -	APVD S BORTNER 100CT94	PRODUCT SPEC			
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	MATERIAL	FINISH	APPLICATION SPEC 114-2162	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
					WEIGHT -	A3	00779	C-322363	-
					CUSTOMER DRAWING	SCALE	SHEET	REV	
						6:1	1 OF 1	M1	