

© 2023 TE Connectivity. All Rights Reserved.


Scale 2:1

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECR-23-184256	17AUG2023	Z.D	Z.Z

Recommend panel dimension(T=3.9mm)
Type 1: For single hole interface


Scale 4:1



Type 2: For multiple hole interface



Recommend Layout(PCB thickness:T=1.6mm)
Scale 4:1



NOTES:

- 1 PACKED IN TRAY ACCORDING TO PACKAGING SPEC. TE03W-0316
- 2 MIN. RETENTION FORCE: 0.5 TAB: 15N 25MM/MIN
- 3 100% ELECTRIC CONTINUITY (LV TEST), SHORT CIRCUIT (HV TEST) AND PRESENCE TESTING

3	2386530-1	HDSCent Shield	CrNi	0.5~2.0µm Ni over Ni-Strike	1
2	2410638-1	HDSCent 180° Header HSG.	PA10T 30GF	Black	1
1	1-2386533-2	0.5x0.4 TAB	CuNiSi	3~6µm Ag OVER Ni	2
ITEM	PART NO.	DESCRIPTION	MATERIAL	FINISH AND COLOR	Qty.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Z.Dong 20JUN2022	 TE Connectivity		
DIMENSIONS: mm		CHK M.Chen 20JUN2022			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD Z.Zhou 20JUN2022			
0 PLC ±0.3 1 PLC ±0.3 2 PLC ±0.2 3 PLC ±0.1 4 PLC ±0.05 ANGLES ±		PRODUCT SPEC 108-94818			
MATERIAL -		APPLICATION SPEC 114-160691	NAME HEADER INSERT ASS 180 DEG		
FINISH -		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-2410640
CUSTOMER DRAWING		SCALE 1:1	SHEET 1 OF 1	RESTRICTED TO -	
				REV B	