















REVISIONS					
P	LTN	DESCRIPTION	DATE	DWN	APVD
A		INITIAL RELEASE	22NOV2022	J.Z	W.Z
A1		REVISE	12JAN2023	J.Z	W.Z
A2		ECR-24-211381	03JUL2024	SDT	W.Z


SPRING
DIFFERENT TOOL DETAILS
FUNCTION AND HANDLING WITH
ALL DETAILS CONTINUOUSLY
SUPPLY BASED ON AVAILABILITY





NOTE-A2

1 ACCORDING INSULATION DIA IS TO CHOOSE THE SINGLE WIRE SEAL

2 VARIANTS WITH GAP-SIZE 0.2mm



3 ADDITIONAL INFORMATION FOR SINGLE WIRE SEAL VARIANTS




A2

PN	DESIGN	MATERIAL	SURFACE	WIRE RANGE [mm ²]	INSULATION Ø [mm]	STRIP FROM WIRE CRIMP	WIRE CRIMP	INSUL.-CRIMP	A	B	C
2434815-2	3	CuFe 2	PRETINNED	0.2-0.5 FLR	1.15-1.6	E = 2.1 G = 2.1 DDr = 0.8	H = 4.3 K = 4.8 DISO = 2.6	2.5	4.4	6.4	
2437299-2	2	CuFe 2	PRETINNED	0.2-0.5 FLR	1.15-1.6	E = 2.1 G = 2.1 DDr = 0.8	H = 2.9 K = 2.9 DISO = 1.4	2.5	4.4	6.4	

ORDER No.	INSULATION Ø	COLOUR
964972-1	1.9-2.1	YELLOW
963530-1	1.4-1.9	GREY
964971-1	1.2-1.6	RED

5:1



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN: J.ZHANG 22NOV2022	CHK: J.GU 22NOV2022	APVD: W.ZHANG 22NOV2022
0-PLC ±0.5	1-PLC ±0.13 ±0.2	NAME: MICRO TIMER 3 CONTACT	PRODUCT SPEC: 108-18386	APPLICATION SPEC: 116-18081
2-PLC ±0.13	3-PLC ±0.013	SIZE: A	CAGE CODE: 00779	DRAWING NO: C=2434815
4-PLC ±0.001	ANGLES	WEIGHT: -	CUSTOMER DRAWING	SCALE: 5:1

TE Connectivity

RESTRICTED TO SHEET 1 OF 1 REV. A2