





DESIGN 1




SECTION B-B




SECTION C-C



SPRING
DIFFERENT TOOL DETAILS
FUNCTION AND HANDLING WITH
ALL DETAILS CONTINUOUSLY
SUPPLY BASED ON AVAILABILITY





FLR-WIRE
DESIGN 2





FLR- AND FLK-CABLE


DESIGN 3




DESIGN 4



SINGLE WIRE SEAL		
964972-1	1.9-2.1	YELLOW
963530-1	1.4-1.9	GREY
964971-1	1.2-1.6	RED
ORDER No.	INSULATION Ø	COLOUR



UNSCALED	PN	DESIGN	MATERIAL	SURFACE	WIRE RANGE [mm ²]	INSULATION Ø [mm]	CRIMP DIMENSION mm			A	B	C
							WIRE CRIMP	INSUL.-CRIMP	STRIP FORM			
SINGLE WIRE SEAL	2435075-2	3	CuFe2		0.5-1.0	1.4-2.1	E=2.5 G=2.7 D _{Dr} =1.2	H=4.3 K=4.8 D _{ISO} =2.7	3.0	4.4	6.4	
	2434742-2	4	CuFe 2		0.2-0.5	1.15-1.6	E=2.1 G=2.1 D _{Dr} =0.8	H=4.3 K=4.8 D _{ISO} =2.6	2.5	4.4	6.4	
	2435080-2	1	CuFe 2	PRETINNED	0.5-1.0	1.4-2.1	E=2.5 G=2.7 D _{Dr} =1.2	H=3.2 K=3.4 D _{ISO} =1.8	3.0	4.4	6.4	
	2435082-2	2	CuFe 2		0.2-0.5	1.15-1.6	E=2.1 G=2.1 D _{Dr} =0.8	H=2.9 K=2.9 D _{ISO} =1.4	2.5	4.4	6.4	



NOTES

ACCORDING TO INSULATION DIA IS TO CHOOSE THE SINGLE WIRE SEAL

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2	OWN: M.BIAN 10NOV2022	CHK: J.GU 10NOV2022	APVD: W.ZHANG 10NOV2022	NAME: MICRO TIMER 2 CONTACT TYPE A PRODUCT GROUP DRAWING
MATERIAL: -	FINISH: -	SIZE: 144-18081	WEIGHT: -	Customer Drawing	RESTRICTED TO: -

SCALE 10:1 SHEET 1 OF 1 REV A3