

4

3

2

1

THIS DRAWING IS UNPUBLISHED.
DIFFUSION RESTREINTE

RELEASED FOR PUBLICATION
LIBRE A LA DIFFUSION


2011

© COPYRIGHT 2011 by Tyco Electronics Corporation


ALL RIGHTS RESERVED.
TOUS DROITS RESERVES

LOC	DIST	REVISIONS				
		P	LTR REV	DESCRIPTION MODIFICATIONS	DATE	DWN DESS
—	—		A	CREATION	05-Sep-14	JG
			B	UPDATED DRAWING	30-Jan-15	PG
			C	ECO-15-006767	19-May-15	JG


F
(No scale)
(Sans échelle)



Sliding
Couissant




Fixed
Fixe



Positionnement fourni par SIMEL sur demande.
Location is provided by SIMEL on request.


Fréquence nominale de l'AMORSIM : 1.21 Hz. ±0.2 Hz
Nominal frequency of the damper : 1.21 Hz. ±0.2 Hz

M12 Stainless steel bolts: 60Nm
Boulons M12 acier inoxydable: 60Nm



Soudé en usine
Factory welded

Soudé en usine
Factory welded



ITEM:

THIS DRAWING IS A CONTROLLED DOCUMENT.
CE PLAN EST UN DOCUMENT CONTRÔLÉ PAR TYCO ELECTRONICS CORPORATION
IL EST SUSCEPTIBLE D'ÊTRE RÉVISÉ. POUR OBTENIR LA DERNIÈRE RÉVISION,
CONTACTER LE SERVICE TECHNIQUE DE TYCO ELECTRONICS SIMEL SAS,
21220 GEVREY-CHAMBERTIN, FRANCE.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED PER TOLERANCES NON SPECIFIEES SELON : -
mm	
MATERIAL MATIERE	FINISH FINITION

DWN /DESSINE GODARD	05-Sep-14
CHK/VERIFIE	-
APVD/APPROUVE	-
PRODUCT SPEC SPEC. PRODUIT	108-69090-001
APPLICATION SPEC SPEC. APPLICATION	-
WEIGHT MASSE APPROX.	9.5 kg

TE *TE connectivity*
SIMEL PRODUCTS

NAME
TITRE 5 AM 82 T250 F121

SIZE FORMAT	CAGE CODE	DRAWING NO No PLAN	RESTRICTED TO RESERVE A
A3	00779	C-2830823	-

CUSTOMER DRAWING	/PLAN CLIENT	UNIQUEMENT POUR REFERENCE	SCALE ECHELLE 1/4	SHEET FEUILLE 1	OF DE 1	REV C
------------------	--------------	------------------------------	----------------------	--------------------	------------	----------