


THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
© COPYRIGHT 20	BY -	ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	29MAR2016	MAO	-
	A1	ECR-16-009563	07JUL2016	MJF	MAO
	A2	ECR-16-014088	05OCT2016	MJF	MJF
	A3	ECR-17-002375	03MAR2017	MJF	MJF

UNIQA-PRO OPTIONS		
PART NUMBER	DESCRIPTION	REFERENCE ASSEMBLY
2844000-1	CRIMP HEIGHT ADJUST, MANUAL	2280870
2844000-2	CRIMP HEIGHT ADJUST, AUTOMATIC	
2844000-3	TERMINAL SCRAP CHOPPER	2282882
2844000-4	POWER PAPER WINDER	
2844000-5	INK JET PRINTER INTERFACE	2280820
2844000-6	1.5 METER MOTORIZED CONVEYOR	2280858
2844000-7	WIRE SPLICE DETECTOR	2280817
2844000-8	LINE VOLTAGE CONVERSION (200, 208, 230V)	2280849
2844000-9	CRIMP FORCE MONITOR, STANDARD (2500LB)	2280860
1-2844000-0	CRIMP FORCE MONITOR, HEAVY DUTY (5000LB)	2280860
1-2844000-1	HOT STAMP MARKER, KIP 20	
1-2844000-2	TABLE FOR TESTER OPTIONS	
1-2844000-3	MICROMETER TESTER	
1-2844000-4	PULL FORCE TESTER, MANUAL	
1-2844000-5	PULL FORCE TESTER, AUTOMATIC	
1-2844000-6	PRODUCTION BATCH LABEL PRINTER	
1-2844000-7	SENCOR - WIRE CORE SENSING	2280861
1-2844000-8	15 DEGREE REEL BRACKET FOR TAB-LOK	
1-2844000-9	SCANNER, 1D BARCODE	
2-2844000-0	SCANNER, 2D QR CODE READER	
2-2844000-1	TU-15 STANDARD TO HD CONVERSION KIT	2280871
2-2844000-2	PF-6 PREFEEDER	
2-2844000-3	CHOPPER BLADE REPLACEMENT KIT	

1. SEE REFERENCE ASSEMBLY DRAWING FOR THE ASSEMBLY DETAILS OF THE ASSOCIATED OPTION.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. ONDO 29MAR2016	 TE Connectivity			
DIMENSIONS:		CHK M. ONDO 29MAR2016				
mm		APVD -	NAME OPTIONS, UNIQA-PRO			
		PRODUCT SPEC	-			
		APPLICATION SPEC				
		-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		WEIGHT	A2	-	©2844000	-
MATERIAL		FINISH	CUSTOMER DRAWING		SCALE 1:1	SHEET 1 OF 1
-		-				REV A3
-		-				