



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	24AUG2023	NK	JDB
	D1	DRAWING RE-CREATED IN CREO	27DEC2023	NK	JDB
	D2	REEL CORE DIA CHANGE	23JUL2024	KA	LET

TAPE ON REEL PACKAGING ACCORDING TO DIN IEC 60286-3
PACKAGING UNIT: 100 PCS









1. DRAWING SPECIFICATION ACCORDING TO DOCUMENT
5_3_16-DOC-1806-00915

2. COPLANARITY OF ALL CLIPS ≤ 0.1MM



1	-	TAPE AND REEL	5
1	-	SOLDER CLIP LEFT	4
1	-	SOLDER CLIP RIGHT	3
5	-	PINS	2
1	-	HOUSING	1
384891-E	REV	DESCRIPTION	ITEM NO.
-	REV OF EACH ASSY NO. (WHEN BLANK, USE DWG. REV)		
QTY	PARTS LIST		

V=TURNED CONTACT (PCB SIDE CAN BE USED WITH POTTED COMPOUND)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N K NIKHIL 10JUL2023	 TE Connectivity			
DIMENSIONS: mm		CHK M SZELAG 13JUL2023				
	TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 2768-mK ISO 8015	APVD J DE BRUIJN 13JUL2023	NAME M12 FEMALE, B CODE, 5P, 17MM SMT V			
		PRODUCT SPEC 108-94887				
		APPLICATION SPEC 114-94781	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO -
		MATERIAL - -	FINISH -	A2	00779	
CUSTOMER DRAWING			SCALE	SHEET	REV	
			5:1	1 of 1	D2	



PCB-LAYOUT PROPOSAL



INSPECTION LEVEL 1: CONTROL CHART REQUIRED
① PROOF OF PROCESS CAPABILITY OR 100% TEST IF
PROCESS CAPABILITY IS NOT ACHIEVED

INSPECTION LEVEL 2 AND 3: CONTROL CHART REQUIRED
② PROOF OF MEAN VALUE, STANDARD DEVIATION AND MACHINE CAPABILITY

③ PROOF OF VALUES OR PROOF OF ATTRIBUTIVE TEST

INFORMATION ON THE SCOPE OF TESTING AND DETECTION BY ERNI VA 7.3.2.3