

4

3

2

1

THIS DRAWING IS UNPUBLISHED DIFFUSION RESTREINTE

RELEASED FOR PUBLICATION LIBRE A LA DIFFUSION

© COPYRIGHT- TE CONNECTIVITY

ALL RIGHTS RESERVED

REVISIONS

REV	DESCRIPTION /MODIFICATIONS	DATE	DWN	APVD
1	NEW DRAWING	24FEB2020		

NOTES

- DIMENSIONS IN mm. a = AS SUPPLIED, b = AFTER FREE RECOVERY
- COATING CODE: /250. MIN THICKNESS: 0.6 mm
- STANDARD LENGTHS P (mm): 250, 500, 750, 1000, 1200 and 1500. OTHER CUT LENGTHS AVAILABLE UNDER REQUEST
- MAXIMUM LONGITUDINAL CHANGE AFTER FREE RECOVERY: -5%/+10%
- STANDARD CUT LENGTH TOLERANCES:
± 5 mm (P ≤ 500)
± 10 mm (P > 500)
- STANDARD PRINTING: LOGO, CRSM, PRODUCT SIZE, BATCH NUMBER

PRODUCT SIZE	APPLICATION RANGE		H		R		S	W	
	MIN	MAX	a min	b max	a min	b max	a min	a min	b min
CRSM 34/10	11	27	35	10	110	35	18	0.3	2.4
CRSM 53/13	17	43	54	13	175	49	18	0.3	2.4
CRSM 84/20	24	68	85	20	270	69	30	0.3	2.4
CRSM 107/29	32	86	108	29	340	90	30	0.3	2.4
CRSM 143/36	39	115	144	36	455	119	30	0.3	2.4
CRSM 198/55	60	160	203	55	640	172	30	0.3	2.4

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWM

CHK

DIMENSIONS:
mmTOLERANCES UNLESS
OTHERWISE SPECI-
FIED:

MATERIAL

FINISH

APVD: Angel Mota

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME
CRSM HEAT SHRINK WRAPAROUND SLEEVESIZE
FORMAT

A3

CAGE CODE

-

DRAWING NO

EPD-202-311923-01

RESTRICTED TO

-

SCALE NTS

SHEET 1

REV 1