







THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	A	ECR-15-018707	13JAN2016	VS DB

CERTIFICATION: UL & CUL FILE NO. E87824					
PRIMARY			SECONDARY		
LEAD NO.	1	2	LEAD NO.	6	7
VOLTAGE	COM	120	VOLTAGE	24	VAC
COLOR	BLK	WHT	COLOR	BLU	YEL
LENGTH	12.0	12.0	LENGTH	12.0	12.0
STRIP LENGTH	.50	.50	STRIP LENGTH	.50	.50

1. ALL LEADS ARE 18AWG UNLESS OTHERWISE SPECIFIED AND HAVE A TOLERANCE OF +1.0/-0
2. STRIP TOLERANCE IS ±1/32.
3. WINDING PROTECTION: INHERENTLY LIMITING.



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ±-
	1 PLC ±.1
	2 PLC ±.03
	3 PLC ±.015
	4 PLC ±-
	ANGLES ±-

MATERIAL	FINISH
-	-

DWN	VIC SLACK	13JAN2016
CHK	D. BLOESCH	13JAN2016
APVD	D. BLOESCH	13JAN2016
PRODUCT SPEC	-	-
APPLICATION SPEC	-	-
WEIGHT	-	-
CUSTOMER DRAWING		

TE Connectivity		NAME		TRANSFORMER OUTLINE
		SIZE	CAGE CODE	DRAWING NO
A3	-	C=4000Y01E07K999		RESTRICTED TO
SCALE		1:1	SHEET	1 OF 1
REV		A		

3-1611471-5
TE PART NO.