



P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	ADHESIVE TAPE WIDTH CHANGED BACK TO 6mm	08FEB2016	SS	PS
	D2	PART OBSOLESCENCE	22MAR2024	KA	SS

TOOLED	PART NUMBER REEL PACKAGING	PART NUMBER BOX PACKAGING	NUMBER OF POSITIONS	"A" MAX	"B"
NO	0-338531-4	7-338531-4	4	8.3	3.81
NO	0-338531-6	7-338531-6	6	10.9	6.35
YES	0-338531-8 	7-338531-8	8	13.4	8.89
NO	1-338531-0	8-338531-0	10	15.9	11.43
NO	1-338531-2	8-338531-2	12	18.5	13.97
NO	1-338531-4	8-338531-4	14	21.0	16.51
NO	1-338531-6	8-338531-6	16	24.0	19.05
NO	1-338531-8	8-338531-8	18	26.1	21.59
NO	2-338531-0	9-338531-0	20	28.6	24.13




SCALE 1:4

BOX PACKAGING
250 PARTNUMBERS PER BOX
FOR ALL PARTNUMBERS.



DETAIL A
SCALE 2:1



SEE DETAIL A






REEL PACKAGING
DEREELING DIRECTION AND CONNECTOR POSITION
2500 CONNECTORS PER REEL FOR ALL PART NUMBERS

2	MALE CONTACT	TIN BRASS	3-5 μ m Sn over 0.5 μ m min Ni
1	HOUSING	G.F POLYESTER, PBT	RED
ITEM NO.	DESCRIPTION	MATERIAL	FINISH / COLOR

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.v.LIEMPT CHK M.v.DRIEL APVD -		22JUN98		 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		Micro Match MALE-ON-BOARD LONG POST, POLARIZED			
		0 PLC ±- 1 PLC ±0.1 2 PLC ±0.20 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH		PRODUCT SPEC 108-19052 APPLICATION SPEC -					
MATERIAL SEE TABLE -		SEE TABLE -		WEIGHT -		SIZE A2	CAGE CODE 00779	DRAWING NO C=338531	RESTRICTED TO -
CUSTOMER DRAWING				SCALE 8:1		SHEET 1 OF 1		REV D2	




$\phi 0.4$ A B
ALL CONTACTS




REFERENCE MATING INTERFACE PATTERN
1.27 STAGGERED PITCH x 1.5 ROW DISTANCE

PC-BOARD HOLE LAYOUT
(COMPONENT SIDE OF BOARD SHOWN)



SCALE 8:1



SCALE 3:1

SHOWN IS A 10
POSITION CONNECTOR.

 OBSOLETE