

SPECIFICATION CONTROL DRAWING

44A0313

WIRE, RADIATION-CROSSLINKED, POLYALKENE-INSULATED,
LIGHTWEIGHT, GENERAL PURPOSE, 2500 VOLT

7-21-08

F

This specification sheet forms a part of the latest issue of Raychem Specification 44.




TABLE I. CONSTRUCTION DETAILS

PART NUMBER ^{1/}	WIRE SIZE (AWG)	CONDUCTOR STRANDING (number x AWG)	DIAMETER OF STRANDED CONDUCTOR (in.)		FINISHED WIRE		
			MINIMUM	MAXIMUM	MAXIMUM RESISTANCE AT 20°C (ohms/1000 ft)	DIAMETER (in.)	MAXIMUM WEIGHT (lbs/1000 ft.)
44A0313-24-*	24	19 x 36	.023	.026	25.9	.057 ± .002	3.0
44A0313-22-*	22	19 x 34	.029	.033	16.0	.069 ± .003	4.3
44A0313-20-*	20	19 x 32	.037	.041	9.77	.078 ± .003	6.1
44A0313-18-*	18	19 x 30	.046	.051	6.10	.088 ± .003	8.7
44A0313-16-*	16	19 x 29	.052	.058	4.76	.097 ± .004	10.9
44A0313-14-*	14	19 x 27	.065	.073	3.00	.115 ± .004	16.2
44A0313-12-*	12	37 x 28	.084	.090	1.98	.131 ± .004	24.2
44A0313-10-*	10	37 x 26	.106	.114	1.24	.161 ± .005	36.5
44A0313-8-*	8	133 x 29	.158	.173	.694	.219 ± .006	65.0
44A0313-6-*	6	133 x 27	.198	.217	.436	.269 ± .007	103.
44A0313-4-*	4	133 x 25	.250	.274	.275	.325 ± .008	158.
44A0313-2-*	2	665 x 30	.320	.340	.177	.404 ± .012	252.
44A0313-0-*	0	1045 x 30	.405	.425	.113	.494 ± .016	380.
44A0313-00-*	00	1330 x 30	.450	.475	.089	.545 ± .016	518.

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.
Tyco Electronics also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

^{1/} COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

The TE logo, Tyco Electronics and Raychem are trademarks.

DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN.
REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.



Raychem Wire & Cable
501 Oakside Avenue
Redwood City, CA 94063-3800
Phone: 1-800-227-8816
Fax: 1-650-361-6297

TABLE II. PERFORMANCE DETAILS

PART NUMBER 1/	BEND TESTING				
	MANDREL DIAMETER (inch) (± 3%)			WEIGHT (lb) (± 3%)	
	IMMERSION LIFE CYCLE AND ACCELERATED AGING	COLD BEND	WRAP	IMMERSION LIFE CYCLE AND ACCELERATED AGING	COLD BEND
44A0313-24-*	.500	1.00	.250	.625	3.00
44A0313-22-*	.750	1.00	.250	2.00	3.00
44A0313-20-*	.750	1.00	.250	2.50	4.00
44A0313-18-*	1.00	1.50	.375	2.50	4.00
44A0313-16-*	1.00	1.50	.375	2.50	5.00
44A0313-14-*	1.50	2.00	.500	2.50	5.00
44A0313-12-*	2.00	2.00	.500	3.00	5.00
44A0313-10-*	3.00	3.00	.750	3.00	5.00
44A0313-8-*	3.00	4.00	.750	6.00	6.00
44A0313-6-*	4.00	5.00	1.00	6.00	10.0
44A0313-4-*	5.00	6.00	1.25	6.00	10.0
44A0313-2-*	6.00	8.00	3.00	6.00	15.0
44A0313-0-*	8.00	10.0	4.00	7.00	15.0
44A0313-00-*	10.0	10.0	5.00	7.00	20.0

WIRE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C

Maximum continuous conductor temperature

VOLTAGE RATING: 2500 volts (rms) at sea level

ACCELERATED AGING: 300 ± 2°C for 6 hours

Identification legibility, 225 ± 2°C for 6 hours

BLOCKING: 150 ± 2°C for 24 hours

COLOR: White preferred

FLAMMABILITY: 30 seconds (maximum); 3 in. (maximum); no flaming of facial tissue

HUMIDITY RESISTANCE: Insulation Resistance, 5000 megohms for 1000 ft. (minimum)

IDENTIFICATION AND COLOR STRIPING DURABILITY:

125 cycles (250 strokes) (minimum), 500 g weight

IMMERSION: Diameter increase 5% (maximum); no cracking, no dielectric breakdown.

INSULATION ELONGATION AND TENSILE STRENGTH:

1.5 inch jaw separation, 2.0 inch/minute crosshead speed

Primary Insulation,

Elongation, 150% (minimum)

Tensile Strength, 2500 lbf/in² (minimum), AWG 24-12

2000 lbf/in² (minimum), AWG 10-00

INSULATION FLAWS:

Primary Insulation,

Spark Test, 5.0 kV (rms)

Impulse Dielectric Test, 6.0 kV (peak)

Finished Wire,

Spark Test, 8.0 kV (rms) at 3 kHz

Impulse Dielectric Test, 13.0 kV (peak)

INSULATION RESISTANCE: 5000 megohms for 1000 ft. (minimum)

LIFE CYCLE: 200 ± 2°C for 168 hours

LOW TEMPERATURE-COLD BEND: -65 ± 2°C for 4 hours

SHRINKAGE: 300 ± 2°C, 0.125 in. (maximum) in 12 in., AWG 24-12

300 ± 2°C, 0.250 in. (maximum) in 12 in., AWG 10-00

SMOKE: 200 ± 2°C. No visible smoke.

SURFACE RESISTANCE: 500 megohms-in. (minimum), both readings

THERMAL SHOCK RESISTANCE: 150 ± 2°C, 0.060 in. (maximum)

VOLTAGE WITHSTAND (Post Environmental): 5000 volts (rms), 60 Hz, 5 minutes

WICKING: 2.25 in. (maximum)

PART NUMBER: The "***" in the part numbers on pages 1 and 2 shall be replaced by color code designators.

1/ Example: AWG 20, white: 44A0313-20-9

AWG 20, white with black stripe: 44A0313-20-90

1/ See footer section on page 1