

REV. B

DCO 131316


TOL. = $\pm.010$

| | |
|-----------------|----------------------------|
| COIL: @ 25°C | |
| RESISTANCE | 1350 OHMS $\pm 10\%$ |
| NOMINAL VOLTAGE | 26.5 VDC |
| MUST OPERATE | 14.5 VDC |
| MUST RELEASE | 8.7 VDC MAX., 1.6 VDC MIN. |

| | |
|--------------|---------------------------|
| ENVIRONMENT: | |
| VIBRATION | 10 Hz TO 3000 Hz @ 30 g's |
| SHOCK | 75 g's 6 MS. DURATION |
| TEMPERATURE | -65 °C TO +125 °C |

NOTES: OPERATE 4 MS MAX.
RELEASE 6 MS MAX.
CONTACT BOUNCE 1.5 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO
2 AMPS 28 VDC RESISTIVE
50,000 OPERATIONS

DR. B.D. 26MAR2007

CK. J.M.B. 9/28/10



Tyco Electronics

©COPYRIGHT 2005

TYCO ELECTRONICS CORPORATION
ALL INTERNATIONAL RIGHTS RESERVED

CUST. QPL
CUST. NO. M39016/38-023L REV.

TE NUMBER
1-1617515-8

CII PART NUMBER

3SBC 1683A2