








REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	27NOV2023	NK	JDB
	B1	DRAWING RE-CREATED IN CREO	27DEC2023	NK	JDB
	B2	REEL CORE DIA CHANGE	25JUL2024	KA	LET
	B3	MATERIAL INFOMRATION ADDED	27SEP2024	SS	LET





PCB-LAYOUT PROPOSAL



SCALE 2:1
3D VIEW



TAPE ON REEL PACKAGING ACCORDING TO DIN IEC 60286-3
PACKAGING UNIT: 100 PCS



- 1. DRAWING SPECIFICATION ACCORDING TO DOCUMENT 5_3_16-DOC-1806-00915
- 2. RETENTION FORCE >20N
- 3. CONTACT AREA MAITING - AND SOLDERING SIDE: 2-1µm Ni-P+0,1-0,2 µm Au (HARD GOLD) AURONIP


1	PS	TAPE & REEL	3
5	COPPER ALLOY. Au PLATED	PINS	2
1	PA. BLACK	HOUSING	1
494081-E	MATERIAL	DESCRIPTION	ITEM NO.
-	REV OF EACH ASSY NO. (WHEN BLANK, USE DWG. REV)		
QTY	PARTS LIST		

INSPECTION LEVEL 1: CONTROL CHART REQUIRED
① PROOF OF PROCESS CAPABILITY OR 100% TEST IF
PROCESS CAPABILITY IS NOT ACHIEVED

INSPECTION LEVEL 2 AND 3: CONTROL CHART REQUIRED
② PROOF OF MEAN VALUE, STANDARD DEVIATION AND MACHINE CAPABILITY

③ PROOF OF VALUES OR PROOF OF ATTRIBUTIVE TEST

INFORMATION ON THE SCOPE OF TESTING AND DETECTION BY ERNI VA 7.3.2.3

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B S ADRUSH 04AUG2023	 TE Connectivity			
DIMENSIONS: mm		CHK M SZELAG 06AUG2023				
	TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 2768-FH ISO 8015	APVD J DE BRUIJN 06AUG2023	NAME M12 FEMALE, A CODE, 5P, 17MM THR			
		PRODUCT SPEC 108-94887	-			
		APPLICATION SPEC 114-94781	-			
MATERIAL -	FINISH -	WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C=494081-E	RESTRICTED TO -
-		CUSTOMER DRAWING			SCALE 5:1	SHEET 1 OF 1