

SPECIFICATION CONTROL DRAWING

SCD


55/2324H

Title TWO CONDUCTOR CABLE, FLAT BRAID SHIELDED, JACKETED,
OUTER SPACE, 600 VOLT

Date 9-27-18

Revision B

This specification sheet forms a part of the latest issue of Raychem Specification 55/.



CABLE CONSTRUCTION DETAILS

PART NUMBER ^{1/}	CONDUCTOR SIZE (AWG)	SHIELD STRAND THICKNESS (± .0004 inch)	JACKET THICKNESS (inch)		OUTSIDE DIAMETER (inch)		MAXIMUM WEIGHT (lbs/1000 ft.)
			MINIMUM	NOMINAL	NOMINAL	MAXIMUM	
55/2324H-30-*	30	.0015	.0040	.0050	.057	.061	2.97
55/2324H-28-*	28	.0015	.0040	.0050	.063	.067	3.69
55/2324H-26-*	26	.0015	.0040	.0050	.072	.076	4.92
55/2324H-24-*	24	.0015	.0040	.0050	.079	.083	5.98
55/2324H-22-*	22	.0015	.0040	.0050	.096	.100	8.84
55/2324H-20-*	20	.0015	.0045	.0055	.118	.122	12.99
55/2324H-18-*	18	.0015	.0045	.0055	.137	.141	18.24
55/2324H-16-*	16	.0015	.0045	.0055	.152	.156	22.45

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 200°C
 Maximum continuous conductor temperature
 VOLTAGE RATING: 600 volts (rms) at sea level
 CROSSLINKED VERIFICATION: 300 ± 3°C for 1 hour
 DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz
 JACKET COLOR: White preferred
 JACKET ELONGATION: 50% (minimum)
 JACKET FLAWS:
 Spark Test, 1000 volts (rms)
 Impulse Dielectric Test, 6.0 kV (peak)
 RADIATION RESISTANCE: 500 megarads
 SHIELD COVERAGE: 90% (minimum)

VACUUM STABILITY:
 Total Mass Loss (TML), 1.00% (maximum)
 Volatile Condensable Material (VCM), 0.10% (maximum)
 VOLTAGE WITHSTAND (Post Environmental):
 1500 volts (rms), 60 Hz, 1 minute

^{1/} PART NUMBER:
 The "*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color.
 Example: AWG 24, blue and white component wires; white jacket: 55/2324H-24-6/9-9

NOTE: Nominal values are for information only. Nominal values are not requirements.

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice. TE Connectivity also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

^{1/} COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

