


SPECIFICATION CONTROL DRAWING

55A2134H

TITLE THREE CONDUCTOR CABLE, FLAT BRAID SHIELDED, JACKETED, GENERAL PURPOSE, 600 VOLT	Date 7-28-08	Revision A
This specification sheet forms a part of the latest issue of Raychem Specification 55A.		



CABLE CONSTRUCTION DETAILS							
PART NUMBER 1/	CONDUCTOR SIZE (AWG)	SHIELD STRAND THICKNESS (± .0004 inch)	JACKET THICKNESS (in.)		OUTSIDE DIAMETER (in.)		MAXIMUM WEIGHT (lbs/1000 ft.)
			MINIMUM	NOMINAL	NOMINAL	MAXIMUM	
55A2134H-30-*	30	.0015	.006	.008	.075	.080	4.8
55A2134H-28-*	28	.0015	.006	.008	.081	.086	5.9
55A2134H-26-*	26	.0015	.006	.008	.092	.097	7.8
55A2134H-24-*	24	.0015	.006	.008	.103	.109	10.1
55A2134H-22-*	22	.0015	.006	.008	.116	.122	13.5
55A2134H-20-*	20	.0015	.006	.008	.131	.139	19.0

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 200°C
 Maximum continuous conductor temperature
VOLTAGE RATING: 600 volts (rms) at sea level
ACCELERATED AGING: 300 ± 3°C for 7 hours
BLOCKING: 200 ± 3°C for 6 hours
DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz
FLAMMABILITY (Procedure 1): 3 seconds (maximum);
 3 in. (maximum); no flaming of facial tissue
JACKET COLOR: White preferred
JACKET ELONGATION AND TENSILE STRENGTH:
 Elongation, 50% (minimum)
 Tensile Strength, 5000 lbf/in² (minimum)
JACKET FLAWS:
 Spark Test, 1.0 kV (rms)
 Impulse Dielectric Test, 6.0 kV (peak)

LIFE CYCLE: 230 ± 3°C for 500 hours
LOW TEMPERATURE-COLD BEND: -65 ± 2°C for 4 hours
SHIELD COVERAGE: 85% (minimum)
VOLTAGE WITHSTAND TEST (Post Environmental):
 1000 volts (rms), 60 Hz, 1 minute

PART NUMBER:
 The "*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color. Colors shown do not necessarily reflect the sequence of manufacturing.
 1/ Example: AWG 24, black, brown and red component wires; white jacket: 55A2134H-24-0/1/2-9

NOTE: Nominal values are for information only.
 Nominal values are not requirements.

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice. Tyco Electronics also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.				
1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx"). OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.				
Page 1 of 1	The TE logo, Tyco Electronics and Raychem are trademarks.			Raychem Wire & Cable 501 Oakeside Avenue Redwood City, CA 94063-3800 Phone: 1-800-227-8816 Fax: 1-650-361-6297
	DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL			
	THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.			