

SPECIFICATION CONTROL DRAWING

SCD

55B1121

Title TWO CONDUCTOR CABLE, SHIELDED, JACKETED,
GENERAL PURPOSE, 600 VOLT

Date 2-20-19

Revision A

This specification sheet forms a part of the latest issue of Raychem Specification 44.




TABLE I. CABLE CONSTRUCTION DETAILS

PART NUMBER 1/	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	JACKET THICKNESS (inch)		OUTSIDE DIAMETER (inch)		MAXIMUM WEIGHT (lbs/1000 ft.)
			MINIMUM	NOMINAL	NOMINAL	MAXIMUM	
55B1121-30-*	30	38	.006	.008	.081	.086	5.5
55B1121-28-*	28	38	.006	.008	.087	.092	6.4
55B1121-26-*	26	38	.006	.008	.097	.102	8.1
55B1121-24-*	24	38	.006	.008	.107	.112	9.9
55B1121-22-*	22	38	.006	.008	.119	.125	12.4
55B1121-20-*	20	38	.006	.008	.133	.140	16.3
55B1121-18-*	18	38	.006	.008	.153	.161	22.1
55B1121-16-*	16	38	.007	.009	.171	.180	27.4
55B1121-14-*	14	38	.007	.009	.205	.215	39.3
55B1121-12-*	12	38	.007	.009	.241	.253	55.4

TABLE II. CABLE PERFORMANCE DETAILS

PART NUMBER 1/	BEND TESTING			
	MANDREL DIAMETER (inch) (± 3%)		WEIGHT (lb) (± 3%)	
	IMMERSION, LIFE CYCLE, AND ACCELERATED AGING	COLD BEND	IMMERSION, LIFE CYCLE, AND ACCELERATED AGING	COLD BEND
55B1121-30-*	3.00	3.00	.125	1.50
55B1121-28-*	3.00	3.00	.125	1.50
55B1121-26-*	3.00	3.00	.125	1.50
55B1121-24-*	3.00	3.00	.250	3.00
55B1121-22-*	3.00	3.00	.375	3.00
55B1121-20-*	6.00	6.00	.500	3.00
55B1121-18-*	6.00	6.00	.500	3.00
55B1121-16-*	6.00	6.00	.750	3.00
55B1121-14-*	6.00	6.00	1.00	9.00
55B1121-12-*	6.00	6.00	1.50	9.00

NOTE: Nominal values are for information only. Nominal values are not requirements.

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.
TE Connectivity also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

Raychem, TE Connectivity, and TE connectivity (logo) are trademarks.

DIMENSIONS ARE IN INCHES AND, UNLESS OTHERWISE DESIGNATED, ARE NOMINAL

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN.
REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.



Raychem Wire & Cable
501 Oakside Avenue
Redwood City, CA 94063-3800
Phone: 1-800-522-6752
Fax: 1-650-361-6297



CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms) at sea level

ACCELERATED AGING: 300 ± 3°C for 6 hours

BLOCKING: 150 ± 3°C for 6 hours

DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz

FLAMMABILITY: 30 seconds (maximum),

3 inches (maximum); no flaming of facial tissue

IMMERSION: Diameter increase 5% (maximum);

no cracking, no dielectric breakdown

JACKET COLOR: White preferred

JACKET CONCENTRICITY: 70% (minimum)

JACKET ELONGATION AND TENSILE STRENGTH:

Elongation, 200% (minimum)

Tensile Strength, 4000 lbf/in² (minimum)

JACKET FLAWS:

Spark Test, 1.5 kV (rms)

Impulse Dielectric Test, 6.0 kV (peak)

LIFE CYCLE: 200 ± 3°C for 168 hours

LOW TEMPERATURE-COLD BEND: -65 ± 2°C for 4 hours

SHIELD COVERAGE: 85% (minimum)

VOLTAGE WITHSTAND (Post Environmental): 1000 volts (rms), 60 Hz, 1 minute

1/ PART NUMBER:

The "" in the part numbers in Tables I and II shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color.

Example: AWG 24, blue and white component wires; white jacket:

55B1121-24-6/9-9

1/ See footer section on page 1.