

4

3

2

1

© 2023 TE Connectivity. All Rights Reserved.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	AF2	REVISED PER ECR-12-013810	24SEP2012	JR	TM
	AF3	REVISED PER ECN-23-233438	02OCT2023	WLS	VS

NOTES:

1 PLATE OVERALL WITH 0.00127 [.000050] MIN NICKEL, THEN TIP PLATE WITH 0.00076 [.000030] MIN GOLD IN THE MATING AREA.

2 PLATE OVERALL WITH 0.00127 [.000050] MIN NICKEL, THEN PLATE IN THE MATING AREA AND STRIPE THE INSIDE OF THE WIRE BARREL WITH 0.00076 [.000030] MIN GOLD.

3. WIRE RANGE: 0.5 - 2mm<sup>2</sup> [20 - 14 AWG].

4. INSULATION RANGE: 3.30 [.130] MAX DIA.

5. APPLICATION TYPE: MINI.

6. DIMENSIONS IN BRACKETS ARE IN INCHES.

1	0.33 [.012] BRASS	61118-7
2	0.33 [.012] PH BZ	61118-6
2	0.33 [.012] BRASS	61118-5
PRE-TIN	0.33 [.012] PH BZ	61118-4
-	0.33 [.012] BRASS	61118-2
PRE-TIN	0.33 [.012] BRASS	61118-1
FINISH	MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. BECK	20NOV1992												
DIMENSIONS: mm [INCHES]		CHK R. SWING	20NOV1992												
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. SELF	09DEC1992												
<table border="1"> <tbody> <tr> <td>0 PLC</td> <td>±-</td> </tr> <tr> <td>1 PLC</td> <td>±-</td> </tr> <tr> <td>2 PLC</td> <td>±0.25 [.010]</td> </tr> <tr> <td>3 PLC</td> <td>±-</td> </tr> <tr> <td>4 PLC</td> <td>±-</td> </tr> <tr> <td>ANGLES</td> <td>±1°</td> </tr> </tbody> </table>		0 PLC	±-			1 PLC	±-	2 PLC	±0.25 [.010]	3 PLC	±-	4 PLC	±-	ANGLES	±1°
0 PLC	±-														
1 PLC	±-														
2 PLC	±0.25 [.010]														
3 PLC	±-														
4 PLC	±-														
ANGLES	±1°														
MATERIAL	FINISH	APPLICATION SPEC 114-1012	WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C-61118	RESTRICTED TO								
-	-	CUSTOMER DRAWING	SCALE 5:1	SHEET 1 OF 1	REV AF3										

1470-19 (3/13)