


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
CE	16	P	LTR	DESCRIPTION	DATE	DWN	APVD
		A		RELEASE PER NPR	25 OCT 05	CSV	JD

- 1 MAXIMUM CONNECTOR INSERTION LOSS IS 0.5 dB PLUS CABLE ATTENUATION OF 1.5dB/km AT 1300nm (SEE TABLE)
- 2 GEOMETRY REQUIREMENTS:
RADIUS OF CURVATURE : 10-30 mm
3. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702



0.65	100.00±1.00	[3937.0±39.0]	9-6374039-9
0.57	50.00±0.50	[1969.0±20.0]	5-6374039-0
0.54	30.00±0.30	[1181.0±12.0]	3-6374039-0
0.53	20.00±0.30	[590.6±12.0]	2-6374039-0
0.52	14.00±0.15	[551.2±6.0]	1-674039-6
0.52	15.00±0.15	[590.6±6.0]	1-6374039-5
0.51	12.00±0.15	[472.4±6.0]	1-6374039-4
0.51	11.00±0.15	[433.1±6.0]	1-6374039-3
0.51	7.00±0.08	[275.6±3.0]	1-6374039-2
0.52	16.45±0.30	[648.0±12.0]	1-6374039-1
0.51	10.00±0.15	[394.0±6.0]	1-6374039-0
0.52	13.41±0.15	[528.0±6.0]	6374039-9
0.51	12.19±0.15	[480.0±6.0]	6374039-8
0.51	9.75±0.15	[384.0±6.0]	6374039-7
0.50	4.57±0.08	[180.0±3.0]	6374039-6
0.51	5.00±0.08	[197.0±3.0]	6374039-5
0.50	3.00±0.05	[118.0±2.0]	6374039-3
0.50	2.00±0.05	[79.0±2.0]	6374039-2
0.50	1.00±0.05	[39.0±2.0]	6374039-1

1 MAX IL (dB)	L	PART NUMBER
---------------	---	-------------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	25 OCT 05	 Tyco Electronics Corporation Harrisburg, Pa 17105-3608																				
DIMENSIONS: METERS [INCHES]		CHK	25 OCT 05																					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	25 OCT 05																					
<table border="0"> <tr><td>0 PLC</td><td>±</td><td>-</td></tr> <tr><td>1 PLC</td><td>±</td><td>-</td></tr> <tr><td>2 PLC</td><td>±</td><td>-</td></tr> <tr><td>3 PLC</td><td>±</td><td>-</td></tr> <tr><td>4 PLC</td><td>±</td><td>-</td></tr> <tr><td>ANGLES</td><td>±</td><td>-</td></tr> <tr><td>FINISH</td><td></td><td></td></tr> </table>		0 PLC	±		-	1 PLC	±	-	2 PLC	±	-	3 PLC	±	-	4 PLC	±	-	ANGLES	±	-	FINISH			NAME
0 PLC	±	-																						
1 PLC	±	-																						
2 PLC	±	-																						
3 PLC	±	-																						
4 PLC	±	-																						
ANGLES	±	-																						
FINISH																								
MATERIAL		PRODUCT SPEC	CABLE ASSEMBLY, FIBER OPTIC, 62.5/125µm PLENUM ZIP, AMP SC DUPLEX FIBER CHANNEL, OPTIMATE																					
		APPLICATION SPEC																						
		WEIGHT	-																					
		CUSTOMER DRAWING	SCALE	NTS																				
		SHEET	1	OF 1																				
		REV	A																					