


© - TE Connectivity. All Rights Reserved.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	B	REVISED PER ECO-19-009164	25JUN2020	SJ DR



1. WIRE RANGE IS FOR 3/0 AWG. STANDARD WIRE CROSS SECTIONAL AREA RANGE: 150,500-190,000 CMA, STRANDED WIRE
  2. TERMINAL BODY MATERIAL THK IS 2.311±0.076 [.091±.003]
  3. RECOMMENDED OPERATING TEMP -55°C(-67°F) TO +200°C(392°F) FOR HEAT SHRINK TUBING.
  4. HEAT SHRINK TUBING SHELF LIFE OF 18 MONTHS FROM DATE CODE ON LABEL.
5. TERMINAL APPLICATION SPECIFICATION 114-2162

1	1-1197706-9	HIGH AND LOW TEMPERATURE CROSS LINKED FLUOROPOLYMER HEAT SHRINK TUBING 25.40[1.00] MIN ID X 50.80±3.05[2.00±.12] RT555-1-0-SP
1	321877-1	TERMINAL BODY: COPPER PER ASTM B152 ANNEALED FINISH: NICKEL PLATE 0.00762[.000300] MIN EXT THK PER SAE AMS QQ-N-290
-1	PART NO	DESCRIPTION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 10DEC09	<b>STE</b> TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK TOM MICHIELUTTI 10DEC09		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD TOM MICHIELUTTI 10DEC09	NAME	
0 PLC ± -		PRODUCT SPEC	HEAT RESISTANT TERMINAL KIT	
1 PLC ± -		APPLICATION SPEC	WIRE SIZE: 3/0 AWG	
2 PLC ± -		5	SIZE	CAGE CODE
3 PLC ± 0.127 [.005]		RESTRICTED TO	DRAWING NO	
4 PLC ± -		WEIGHT	A3 00779 C-696654	
ANGLES ± 1°		CUSTOMER DRAWING	SCALE	SHEET
MATERIAL SEE TABLE	FINISH SEE TABLE	4:1		1 OF 1
		REV		B