


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
P4		LC20-0029-10 / ECO-10-004113	10FEB2010	DM	BJ
P3		LC20-0083-16 / ECO-16-011577	19JUL2016	JG	BJ
P4		LC20-0002-20 / ECO-20-000283	23JAN2020	DM	BJ



1. DIMENSIONS ARE FOR REFERENCE ONLY
2. INHIBITOR IS APPLIED AT FACTORY TO GROOVES OF 'C' BODY AND WEDGE
3. WIRE SIZES ARE MARKED ON WEDGE
4. USE BLUE SHELLS PART NO. 69338-1
5. PART NO. 600468 IS SHOWN.

SUPERSEDED BY 2365256-1	3.9	5.6	6.6	#2 AWG	#4 - 3/0 AAC	600468-2
ACTIVE	2.5	4.6	5.5	#2 AWG	2/0, 3/0 ACSR/AAC	600468
STATUS	C	B	A	BAIL SIZE	RUN CONDUCTOR RANGE	PART NO.

QUANTITY	DESCRIPTION	ITEM NO
1	LABEL	4
1	BAIL, COPPER, TIN PLATED	3
1	WEDGE, ALUMINUM ALLOY	2
1	C BODY, ALUM ALLOY	1
-2	DESCRIPTION	ITEM NO
PARTS LIST		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. CHOW 27JUL98																
DIMENSIONS: MM [INCHES]		CHK H. HENRY 28JUL98																
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. HANNA 28JUL98	NAME STIRRUP ASSEMBLY, AMPACT, BLUE CODED, #2 BAIL															
<table border="0"> <tr> <td>0 PLC</td> <td>± -</td> </tr> <tr> <td>1 PLC</td> <td>± -</td> </tr> <tr> <td>2 PLC</td> <td>± -</td> </tr> <tr> <td>3 PLC</td> <td>± -</td> </tr> <tr> <td>4 PLC</td> <td>± -</td> </tr> <tr> <td>ANGLES</td> <td>± -</td> </tr> </table>		0 PLC	± -	1 PLC	± -	2 PLC	± -	3 PLC	± -	4 PLC	± -	ANGLES	± -	PRODUCT SPEC -	SIZE A3	CAGE CODE 00779	DRAWING NO C=600468	RESTRICTED TO -
0 PLC	± -																	
1 PLC	± -																	
2 PLC	± -																	
3 PLC	± -																	
4 PLC	± -																	
ANGLES	± -																	
MATERIAL SEE BOM		FINISH -	WEIGHT -	CUSTOMER DRAWING														
			SCALE NTS	SHEET 1 OF 1	REV P4													