# CHEMINAX

75 OHM, AWG 20, 19 STRANDS OF AWG 32 COAXIAL CABLE

Date:

11-20-96


В

Revision:

THIS SPECIFICATION SHEET FORMS A PART OF THE LATEST ISSUE OF RAYCHEM SPECIFICATION 1200.

### CONSTRUCTION DETAILS

DIMENSIONS ARE NOMINAL VALUES IN INCHES UNLESS OTHERWISE DESIGNATED



Outer jacket color will be black (designated by a "0" appended to the part number, e.g., 7520A1311-0) unless otherwise specified.

Designate outer jacket color with a dash number in accordance with MIL-STD-681.

## **ELECTRICAL CHARACTERISTICS**

CHARACTERISTIC IMPEDANCE

75 ± 3 ohms, Method B

CAPACITANCE

17.1 pF/ft. (nominal) at 1 kHz

18.5 pF/ft. (maximum) at 1 kHz

**VELOCITY OF PROPAGATION** 

79% (nominal)

## ADDITIONAL REQUIREMENTS

#### ELECTRICAL

CONDUCTOR RESISTANCE INSULATION RESISTANCE

9.53 ohms/1000 ft. (nominal)

10,000 megohms (minimum)

for 1000 ft.

JACKET FLAWS SPARK TEST

1.0 kV (rms), 60 Hz IMPULSE TEST 6.0 kV (peak)

**VOLTAGE WITHSTAND** 

(DIELECTRIC)

1000 volts (rms), (minimum)

#### **ENVIRONMENTAL**

AGING STABILITY **FLAMMABILITY** 

135°C/-55°/7.00 inch mandrel

Method C **HEAT SHOCK** 225°C

LOW TEMPERATURE-COLD BEND

-55°C/7.00 inch mandrel

**VOLTAGE WITHSTAND** 

(POST ENVIRONMENTAL) 1000 volts (rms), 1 minute

#### **PHYSICAL**

INSULATION (DIELECTRIC)

**ELONGATION** TENSILE STRENGTH

**JACKET** 

**ELONGATION** TENSILE STRENGTH JACKET THICKNESS SHIELD COVERAGE

50% (minimum) 800 lbf/in2 (minimum)

100% (minimum) 2000 lbf/in² (minimum) .020 inch (nominal)

90% (minimum)

WEIGHT

29.0 lbs/1000 ft. (nominal)

