






REVISIONS				
P	LTN	DESCRIPTION	DATE	APVD
0		RELEASED PER 0G3B-0380-01	23OCT2001	KW SR
A		RELEASED PER ECR-21-117154	08AUG2022	SM VS


- PARTS COMPLY TO AMP SOLDERABILITY SPECIFICATION 109-11-3.
- CIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES, BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.
- DIMENSIONS IN BRACKETS ARE IN INCHES.
- DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY CONDITION. ADDITIONAL 2% GROWTH DUE TO END USE LOCATION MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.



SECTION A-A



RECOMMENDED MOUNTING HOLE PATTERN FOR 1.57 [.062] THICK P.C. BOARD



3 DIMENSIONAL MODEL SCALE 4:1

PHOSPOR BRONZE, PRE-TIN PIN CONTACT MATERIAL AND FINISH	NYLON, UL94V-2, NATURAL HOUSING MATERIAL AND COLOR	794891-1 PART NUMBER
--	---	-------------------------



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: K. WHITAKER 08-JAN-2001 CHK: S. RIDGILL 08-JAN-2001 APVD: S. RIDGILL 08-JAN-2001	TE TE Connectivity NAME: SOCKET HEADER ASSEMBLY, POLARIZED, 4 CIRCUIT, W/O DRAIN HOLES, UNIVERSAL MATE-N-LOK SIZE: CAGE CODE DRAWING NO: A100779C=794891 RESTRICTED TO:
DIMENSIONS: mm [INCHES] 0 PLC ± 1 PLC ± 2 PLC ±0.131(.005) 3 PLC ± 4 PLC ± ANGLES FINISH: ±0°30'	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ±0.131(.005) 3 PLC ± 4 PLC ± ANGLES FINISH: ±0°30'	APPLICATION SPEC: - WEIGHT: - CUSTOMER DRAWING:	
MATERIAL: SEE TABLE		SEE TABLE	SCALE: 5:1 SHEET 1 OF 1 REV A