





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
C1		ECR-19-014657	13DEC2020	RR	SZ

1. MATERIAL: HOUSING - HIGH TEMPERATURE NYLON, COLOR: BLACK, UL 94-V0  
 OVERMOLDED TERMINAL ARRAY - PBT, BROWN  
 TERMINALS - 0.33[.013] THICK PHOS BRONZE  
 PLATED WITH 1.27 $\mu$ m[.000050] MINIMUM THICK  
 HARD GOLD IN LOCALIZED AREA AND 3.81 $\mu$ m  
 [.000150] MINIMUM THICK MATTE TIN IN SOLDER  
 AREA OVER 1.27 $\mu$ m[.000050] MINIMUM THICK  
 NICKEL UNDERPLATE.

△ JACK CAVITY CONFORMS TO FCC RULES AND  
 REGULATIONS, PART 68 SUBPART F.

△ USE #30 DRILL BIT OR 3.25mm DRILL BIT WHEN  
 PRODUCING THESE PCB HOLES.



SUGGESTED PANEL CUTOUT

SUGGESTED PC BOARD LAYOUT  
 COMPONENT SIDE

3.05±0.38 [.120±.015]	6116518-2
3.56±0.38 [.140±.015]	6116518-1
DIM "A"	
PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	21MAY2005	DL DRUMMOND/L.A.MAYER	
DIMENSIONS: mm [INCHES]		CHK	21MAY2005	J.WESTMAN	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	21MAY2005	S.FLICKINGER	
0 PLC	± -	PRODUCT SPEC		NAME	
1 PLC	± -	108-1163-2		MODULAR JACK ASSEMBLY, 8 POSITION, RIGHT ANGLE, LOW PROFILE, CATEGORY 5e	
2 PLC	± 0.25[.010]	APPLICATION SPEC		SIZE	CAGE CODE
3 PLC	± -	114-2048		DRAWING NO	RESTRICTED TO
4 PLC	± -	WEIGHT	0.000000	A2 00779	C=6116518
ANGLES	± -	CUSTOMER DRAWING		SCALE	SHEET
MATERIAL	FINISH	SEE NOTE 1		4:1	1 OF 1
SEE NOTE 1	SEE NOTE 1			REV	C1