

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

REVISIONS

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECR-16-008648	16JUN2016	WZ	GG



NOTES:

- PACKAGED IN PRINTED ZIPLOCK POLYBAG.
- LABEL ON POLYBAG TO READ AS FOLLOWS:  

621783-1 AT ADAPTER (DB9M/DB25F)
-------------------------------------
- WRAP FOIL OVER PRE-MOLD 360° FROM CONNECTOR SHELL TO SHELL.
- IF USING ALUMINUM MYLAR FOIL, ALUMINUM MUST BE FACING INWARD.
- THIS PRODUCT IS PRODUCED IN COMPLIANCE WITH ANSI/ASQC Z1.4-1993, TO AN INSPECTION LEVEL III, WITH A NORMAL SAMPLING PLAN.
- TEST REQUIREMENT:  
 CONTINUITY RESISTANCE: 1 ohm MAX,  
 INSULATION RESISTANCE: 50 M ohm MIN.  
 HI-POT TEST: DC 300V/0.01 Sec MIN.
- PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ENVIRONMENTAL STANDARD 230-702.

TE P/N: 621783-1

P1	P2
1	8
2	3
3	2
4	20
5	7
6	6
7	4
8	5
9	22
SHELL	1+SHELL

1	PC	DB25 FEMALE, SOLDER TYPE, CONTACT: GOLD FLASH, SHELL: NICKEL PLATED, INSULATION COLOR: BLACK.	9
AR	MR	UL1007 28AWG, COLOR: BLACK.	8
AR	MR	ALUMINUM FOIL, W: 35.0MM.	7
AR	KG	INNER MOLD PE.	6
AR	KG	MOLD PVC, 40P, COLOR: BEIGE(BG01).	5
AR	KG	MOLD PVC, 30P, COLOR: BEIGE(BG01).	4
4	PC	#4-40 THUMBSCREW.	3
2	PC	#4-40 HEX NUT, 5.0*6.0MM.	2
1	PC	DB9 MALE, SOLDER TYPE, CONTACT: GOLD FLASH, SHELL: INSULATION COLOR: BLACK.	1
QTY	U/M	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.EISENTRAU 12-16-96	<b>TE Connectivity</b> ADAPTER, DB9 MALE TO DB25 FEMALE, OVERMOLDED											
DIMENSIONS: mm		CHK R.CAPP 12-20-96												
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D.WILSON 12-20-96												
<table border="0"> <tr><td>0 PLC</td><td>± -</td></tr> <tr><td>1 PLC</td><td>± -</td></tr> <tr><td>2 PLC</td><td>± -</td></tr> <tr><td>3 PLC</td><td>± -</td></tr> <tr><td>4 PLC</td><td>± -</td></tr> <tr><td>ANGLES</td><td>± -</td></tr> </table>		0 PLC				± -	1 PLC	± -	2 PLC	± -	3 PLC	± -	4 PLC	± -
0 PLC	± -													
1 PLC	± -													
2 PLC	± -													
3 PLC	± -													
4 PLC	± -													
ANGLES	± -													
MATERIAL		PRODUCT SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO								
FINISH		APPLICATION SPEC	A300779		C-621783	-								
-		WEIGHT	0.000000		CUSTOMER DRAWING									
		SCALE	N.T.S		SHEET	1 OF 1								
					REV	B								