






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H7	REVISED PER ECR-23-173068	05DEC2023	P.C	D.Z

- 1 WIRE RANGE: 0.3-0.82mm<sup>2</sup> (22-18 AWG)
- 2 INSULATION RANGE: 1.50 - 3.10 DIA.
- 3 FINISH: 1.27μm MINIMUM NICKEL ALL OVER.
- 4 FINISH: 0.76μm MIN GOLD ON INNER SURFACE, PERMITTED ON OUTER SURFACE.
- 5 FINISH: 2.54μm MINIMUM TIN ON ALL SURFACES IN THIS AREA
- 6 FINISH: 2.54μm MINIMUM PRE-TIN ALL OVER
- 7 CONTACTS COATED WITH ANTI-FRETTING LUBRICANT



SECTION C-C

TIN	6 7	BRASS	794955-5
GOLD	3 4	PHOS. BRZ.	794955-4
PRE-TIN	6	PHOS. BRZ.	794955-3
GOLD	3 4	BRASS	794955-2
PRE-TIN	6	BRASS	794955-1
FINISH		MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HAMM 07-SEP-2001			
DIMENSIONS: mm		CHK D. COLEY 07-SEP-2001			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. COLEY 07-SEP-2001	NAME S. HAMM		
0 PLC ± -		PRODUCT SPEC 108-2112	TERMINAL PIN VAL-U-LOK(TM)		
1 PLC ± 0.25		APPLICATION SPEC 114-13172	SIZE A2	CAGE CODE 00779	DRAWING NO C=794955
2 PLC ± 0.15		MATERIAL	SCALE N/A	SHEET 1 of 1	RESTRICTED TO -
3 PLC ± -		FINISH	CUSTOMER DRAWING		
4 PLC ± -		WEIGHT -	REV H7		
ANGLES ±					