

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

REVISIONS

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

P	LTR	DESCRIPTION	DATE	DWN	APVD
	E	ECR-16-008648	16JUN2016	WZ	GG



PIN ASSIGNMENT :

DB9 F.	1	2	3	4	5	6	7	8	9	Shell
										Drain
DB9 M.	1	2	3	4	5	6	7	8	9	Shell

621808-2	120.0 <sup>+6.00</sup> / <sub>-2.00</sub>	10	2 OHM MAX
621808-1	72.0 <sup>+6.00</sup> / <sub>-2.00</sub>	6	1 OHM MAX
PART NO.	"L" LENGTH	LABEL XX'	CONTINUITY RESISTANCE

NOTES:

- PACKAGED IN CTG STANDARD PRINTED ZIPLOCK POLYBAG.
- LABEL INFORMATION AS FOLLOWS:  

621808-XX
1938943000A
- TEST REQUIREMENT:  
CONTINUITY RESISTANCE: SEE TABLE.  
INSULATION RESISTANCE: 50 M ohm MIN.  
HI-POT TEST: DC 300V/0.01 Sec MIN.
- PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TE CONNECTIVITY ENVIRONMENTAL STANDARD 230-702.

QTY	U/M	DESCRIPTION	ITEM
1	PC	DB9 FEMALE, SOLDER TYPE, CONTACT: GOLD FLASH, INSULATION COLOR: BLACK. RoHS.	9
1	PC	LABEL, SIZE: 25.0*35.0MM, WHITE: 25.0*13.0MM.	8
AR	MR	UL2464 9C*28AWG+AL/FOIL+DRAIN, COLOR: BEIGE.	7
2	PC	#4-40 THUMBSCREW.	6
AR	KG	MOLDED PVC, 30P, COLOR: BEIGE.(BG01).	5
AR	MR	HEAT SHRINK TUBING, 1.5MM, COLOR: BLACK.	4
AR	KG	OVER MOLD PVC, 40P, COLOR: BEIGE.(BG01).	3
AR	KG	INNER MOLD PE	2
1	PC	DB9 MALE, SOLDER TYPE, CONTACT: GOLD FLASH, INSULATION COLOR: BLACK. RoHS.	1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.EISENTRAUT 11-19-96	<b>TE Connectivity</b>														
DIMENSIONS: INCHES		CHK STEVEN ZHOU 8JUN06															
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD SINGOL HE 8JUN06	NAME CABLE ASSY, DB9 FEMALE TO MALE, OVERMOLDED														
<table border="1"> <tr> <td>0 PLC</td> <td>± -</td> </tr> <tr> <td>1 PLC</td> <td>± -</td> </tr> <tr> <td>2 PLC</td> <td>± -</td> </tr> <tr> <td>3 PLC</td> <td>± -</td> </tr> <tr> <td>4 PLC</td> <td>± -</td> </tr> <tr> <td>ANGLES</td> <td>± -</td> </tr> </table>		0 PLC	± -	1 PLC	± -	2 PLC	± -	3 PLC	± -	4 PLC	± -	ANGLES	± -	PRODUCT SPEC	SIZE		
0 PLC	± -																
1 PLC	± -																
2 PLC	± -																
3 PLC	± -																
4 PLC	± -																
ANGLES	± -																
MATERIAL		APPLICATION SPEC	CAGE CODE	DRAWING NO	RESTRICTED TO												
FINISH		WEIGHT 0.000000	A300779	C-621808	-												
CUSTOMER DRAWING			SCALE 1:1	SHEET 1 OF 1	REV E												