


NUMMER	828652
VERWENDET FÜR	
WAR NR.	86-9753-8

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	A3	PART OBSOLESCENCE	26MAR2024	KA SS

POLZ.	L±0.4	BESTELL-NR.
1	2.54	828 652-1 ^{△3}
2	5.08	-2 ^{△3}
3	7.62	^{△2} 828 652-3
4	10.16	828 652-4 ^{△3}
5	12.70	-5
6	15.24	-6
7	17.78	-7
8	20.32	-8
9	22.86	-9
10	25.40	1- -0
11	27.94	1- -1
12	30.48	1- 828 652-2 ^{△3}
13	33.02	1- -3
14	35.56	1- -4
15	38.10	1- -5
16	40.64	1- -6
17	43.18	1- -7
18	45.72	1- -8
19	48.26	1- -9
20	50.80	2- -0
21	53.34	2- -1
22	55.88	2- -2
23	58.42	2- -3
24	60.96	2- -4
25	63.50	2- -5
26	66.04	2- -6
27	68.58	2- -7
28	71.12	2- -8
29	73.66	2- -9
30	76.20	3- -0
31	78.74	3- -1
32	81.28	3- -2
33	83.82	3- -3
34	86.36	3- -4
35	88.90	3- -5
36	91.44	3- -6
37	93.98	3- -7
38	96.52	3- -8
39	99.06	3- -9
40	101.60	4- -0
41	104.14	4- -1
42	106.68	4- -2
43	109.22	4- -3
44	111.76	4- -4
45	114.30	4- -5
46	116.84	4- -6
47	119.38	4- -7
48	121.92	4- 828 652-8
49	124.46	4- -9
50	127.00	5- 828 652-0



- △1 MIN. 2.0µm ZINN ÜBER 1.27µm NICKEL
- △2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- △3 OBSOLETE

TE Connectivity. All Rights Reserved. 2024

CAD-ORIGINAL
ZEICHNUNG NICHT ÄNDERN

KONTAKTSTIFT	Cu Sn	^{△1}
STIFTGEHÄUSE	PBTP-GV	GRÜN
BENENNUNG	WERKSTOFF	OBERFLÄCHE FARBE

ZEICHNUNG GÜLTIG AB KW 44/93

DIMENSIONS: mm	DWN WRULICH	31.08.89	MATERIAL -	FINISH -
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2 mm	CHK SCHAAR.	-	TE Connectivity	
0 PLC ± -	APVD -	-		
1 PLC ± -	PRODUCT SPEC	-	NAME AMPMODU II STIFTLAISTE	
2 PLC ± -	APPLICATION SPEC	-	EINREIHIG	
3 PLC ± -	WEIGHT	0	SIZE A4	CAGE CODE 00779
4 PLC ± -			DRAWING NO C-828652	RESTRICTED TO -
ANGLES ± -			SCALE 4:1	SHEET 1 OF 1
	CUSTOMER DRAWING			REV A3