

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT - By -

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
CE	16	D	ECR-14-011637	22AUG2014	HZ RZ

- 1. MAXIMUM CONNECTOR INSERTION LOSS IS 0.2dB PLUS CABLE ATTENUATION OF 0.7dB/km AT 1310nm. (SEE TABLE)
- 2. MINIMUM RETURN LOSS: 55 dB
- 3. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TE STANDARD TEC-138-702.



0.20	0.40+0.05/-0.0 [15.74+2.00/-0.0]	1-6374110-1
0.21	10.00±0.15 [393.70±6.0]	1-6374110-0
0.20	2.60±0.05 [102.3±2.0]	6374110-9
0.20	1.63±0.05 [64.0±2.0]	6374110-8
0.20	0.476±0.040 [18.8±1.6]	6374110-7
0.20	0.343±0.040 [13.5±1.6]	6374110-6
0.20	5.00±0.08 [196.90±3.00]	6374110-5
0.20	4.00±0.08 [157.50±3.00]	6374110-4
0.20	3.00±0.05 [118.10±2.00]	6374110-3
0.20	2.00±0.05 [78.70±2.00]	6374110-2
0.20	1.00±0.05 [39.40±2.00]	6374110-1
MAX IL (dB)	L	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KATHY HE 28SEP05	TE TE Connectivity													
DIMENSIONS: METERS [INCHES]		CHK RICHARD ZHAO 28SEP05														
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J.DUNCAN 28SEP05	NAME CABLE ASSY, FIBER OPTIC, 2.0mm , SM LC TO LC, OPTIMATE													
<table border="0"> <tr> <td>0 PLC</td><td>± -</td></tr> <tr> <td>1 PLC</td><td>± -</td></tr> <tr> <td>2 PLC</td><td>± -</td></tr> <tr> <td>3 PLC</td><td>± -</td></tr> <tr> <td>4 PLC</td><td>± -</td></tr> <tr> <td>ANGLES</td><td>± -</td></tr> </table>		0 PLC	± -	1 PLC	± -	2 PLC	± -	3 PLC	± -	4 PLC	± -	ANGLES	± -	PRODUCT SPEC -	-	
0 PLC	± -															
1 PLC	± -															
2 PLC	± -															
3 PLC	± -															
4 PLC	± -															
ANGLES	± -															
MATERIAL -		FINISH -	APPLICATION SPEC -	RESTRICTED TO -												
		WEIGHT -	SIZE A3	CAGE CODE 00779												
		DRAWING NO C-6374110		SCALE NTS												
		CUSTOMER DRAWING		SHEET 1 OF 1												
				REV D												