


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
DF	SO	B	REV PER ECR-05-012024	25OCT05	TK CT



1. MARKED PER MIL-STD-130 .09 HIGH CHARS.
  2. TO MATE WITH AMP LGH-1/2L RECEPTACLE WITH .89 [22.6] BARREL DEPTH.
  3. OPERATING VOLTAGE: 15 KVDC AT 0 TO 70,000 FEET, -55° C TO 125 ° C.
- △4 PIGTAIL IS SOLDER DIPPED.  
 △5 INSULATION CUT BUT NOT REMOVED.

△5	5-868489-1
△4	868489-1
REMARKS	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 5-17-90	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		CHK M.GARDNER 5-20-90		
		APVD M.GARDNER 5-20-90	NAME LEAD ASS'Y, POS STOP, SGL. END, LGH-1/2L (BROWN)	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	SIZE A3	
0 PLC ± -		APPLICATION SPEC	CAGE CODE 00779	DRAWING NO C-868489
1 PLC ± -		WEIGHT	RESTRICTED TO	
2 PLC ± .02 [0.5]		CUSTOMER DRAWING	SCALE 2:1	SHEET 1 of 1
3 PLC ± -			REV B	
4 PLC ± -				
ANGLES ± -				
MATERIAL SEE CALLOUTS				
FINISH SEE CALLOUTS				