


THIS SPECIFICATION SHEET FORMS A PART OF THE LATEST ISSUE OF RAYCHEM SPECIFICATION 1200.

CONSTRUCTION DETAILS

DIMENSIONS ARE NOMINAL VALUES IN INCHES UNLESS OTHERWISE DESIGNATED.



ELECTRICAL CHARACTERISTICS

| | |
|--------------------------|--------------------------------|
| CHARACTERISTIC IMPEDANCE | 95 ± 5 ohms, Method B |
| CAPACITANCE | 13.5 pF/ft. (nominal) at 1 kHz |
| VELOCITY OF PROPAGATION | 79% (nominal) |

ADDITIONAL REQUIREMENTS

ELECTRICAL

| | |
|---|---------------------------------------|
| CONDUCTOR RESISTANCE | 198. ohms/1000 ft. (nominal) |
| INSULATION RESISTANCE (CONDUCTOR TO SHIELD) | 10,000 megohms (minimum) for 1000 ft. |
| JACKET FLAWS | |
| SPARK TEST | 1.0 kV (rms) |
| IMPULSE TEST | 6.0 kV (peak) |
| VOLTAGE WITHSTAND CONDUCTOR TO SHIELD | 1000 volts (rms) (minimum) |
| SHIELD TO SHIELD | 500 volts (rms) (minimum) |

ENVIRONMENTAL

| | |
|--|--------------------------------|
| FLAMMABILITY | Method B |
| HEAT SHOCK | 225°C |
| LOW TEMPERATURE COLD BEND | -55°C/3.25 inch mandrel |
| VOLTAGE WITHSTAND (POST ENVIRONMENTAL) | 1000 volts (rms), for 1 minute |

PHYSICAL

| | |
|------------------------------------|------------------------------------|
| INSULATION (DIELECTRIC) ELONGATION | 50% (minimum) |
| TENSILE STRENGTH | 800 lbf/in ² (minimum) |
| 1 ST JACKET ELONGATION | 200% (minimum) |
| TENSILE STRENGTH | 2000 lbf/in ² (minimum) |
| 2 ND JACKET ELONGATION | 200% (minimum) |
| TENSILE STRENGTH | 4000 lbf/in ² (minimum) |
| 1 ST JACKET THICKNESS | .010 inch (nominal) |
| 2 ND JACKET THICKNESS | .008 inch (nominal) |
| SHIELD COVERAGE (EACH) | 90% (minimum) |

| | |
|--------|-----------------------------|
| WEIGHT | 11.7 lbs/1000 ft. (nominal) |
|--------|-----------------------------|

Outer jacket color will be white (designated by a "-9" appended to the part number, e.g. 9532A5114-9) unless otherwise specified.

Designate outer jacket color with a dash number in accordance with MIL-STD-681. Other codes and suffixes may be added to the part number, as necessary, to capture any additional requirements imposed by the purchase order.

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.

Tyco Electronics also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.