


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	NOTE 1 0.76μm PLATING UPDATE (PdNi+AuFLASH)	12JUL2023	BGC	PS

CONTACT PIN	CuZn	
PINCASE	PBTP-GV	GREEN
DESCRIPTION	WERKSTOFF	SURFACE COLOR

PARTS PER ROW	L±0.5	PART NO.
-	-	-
2	5.08	-2
3	7.62	-3
4	10.16	-4
5	12.70	-5
6	15.24	-6
7	17.78	-7
8	20.32	966530 -8
9	22.86	-9
10	25.40	1-0
11	27.94	1-1
12	30.48	1-2
13	33.02	1-3
14	35.56	1-4
15	38.10	1-5
16	40.64	1-6
17	43.18	1-7
18	45.72	1-8
19	48.26	1-9
20	50.80	2-0
21	53.34	2-1
22	55.88	2-2
23	58.42	2-3
24	60.96	2-4
25	63.50	2-5
26	66.04	2-6
27	68.58	2-7
28	71.12	2-8
29	73.66	2-9
30	76.20	3-0
31	78.74	3-1
32	81.28	3-2
33	83.82	3-3
34	86.36	3-4
35	88.90	3-5
36	91.44	3-6
37	93.98	3-7
38	96.52	3-8
39	99.06	3-9
40	101.60	4-0
41	104.14	4-1
42	106.68	4-2
43	109.22	4-3
44	111.76	4-4
45	114.30	4-5
46	116.84	4-6
47	119.38	4-7
48	121.92	4-8
49	124.46	4-9
50	127.00	5-0



- OBSOLETE
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- MATING SIDE: Min 0.76μm (PdNi + Au FLASH) IN ZONE "F" OVER Min 1.27μm Ni (Alternative plating - Min 0.76μm Au OVER Min 1.27μm Ni) SOLDER SIDE: 3-5μm TIN OVER Min 1.27μm Ni.

TE Connectivity. All Rights Reserved.



DIMENSIONS: mm	DWN A.HO	12AUG1994	MATERIAL	-	FINISH	-						
	CHK M.SCHAARSCHMIDT	12AUG1994	TE Connectivity									
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2 mm	APVD -	-					NAME SPEC. AMPMODU II PIN HEADER, DUAL ROW					
0 PLC ± -	PRODUCT SPEC	108-18012	SIZE	A4	CAGE CODE	00779	DRAWING NO	C-966530	RESTRICTED TO	-		
1 PLC ± -	APPLICATION SPEC	-	WEIGHT	-	CUSTOMER DRAWING		SCALE	4:1	SHEET	1 OF 1	REV	B1
2 PLC ± -												
3 PLC ± -												
4 PLC ± -												
ANGLES ± -												

