


THIS DRAWING IS UNPUBLISHED. VERTRAULICHE UNVEROEFFENTLICHTE ZEICHNUNG. BY AMP INCORPORATED. ALL RIGHTS RESERVED. ALLE RECHTE VORBEHALTEN.

MATED WITH: PASSEND ZU:	LOC AI	DIST -	REVISIONS AENDERUNGEN					
-			P	LTR	DESCRIPTION BESCHREIBUNG	DATE	DWN	APVD
PROJEKT NR.: -				A2	SEE EG00-2458-99	16DEC99	VB	-

SEE TABLE DRAWING 1241639

-	-	-	-	-	-	-	-
CUSTOMER PART NO	AMP PART NO	REV.	PCS.	MATERIAL	SURFACE COLOR	DESCRIPTION	
DIMENSIONS: DIMENSIONEN: mm		DWN v/d Burgt 12 NOV 99	MATERIAL		FINISH OBERFLAECHE/FARBE -		
TOLERANCES UNLESS OTHERWISE SPECIFIED; ALLGEMEINTOLERANZEN n. ISO 8015 n. ISO 2768 - mH -E n. DIN 16901 - 140		CHK D. Kuempel 12 NOV 99	AMP Deutschland GmbH D - 63225 Langen		AMP		
		APVD -					
ANGLES/WINKEL ±-		PRODUCT SPEC 108-18476-1	NAME		POWER QUADLOK, PIN CONTACT Power Quadlok, Stiftkontakt		
		APPLICATION SPEC 114-18141-1	SIZE	CAGE CODE	DRAWING NO ZEICHNUNGS-NR.	RESTRICTED TO NUR FUER	
WEIGHT GEWICHT -		A4	00779	C-968133	-		
		CUSTOMER DRAWING /KUNDENZEICHNUNG		MASSSTAB -	BLATT 1 OF VON 1	A2	