


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	16MAY2023	BDA	MB



PRODUCT DIMENSIONS

PART	AS SUPPLIED				AS RECOVERED							
	MINIMUM INSIDE DIAMETER (D)		MAXIMUM INSIDE DIAMETER (D)		MAXIMUM INSIDE DIAMETER (d)		NOMINAL TOTAL WALL THICKNESS (W)		WALL THICKNESS TOLERANCE		NOMINAL MELTABLE WALL THICKNESS (WI)	
	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.
ATUM-175/ 155-0-STK	3.94	0.155	4.44	0.175	1.00	0.039	1.00	0.039	0.30	0.012	0.50	0.020


PRODUCT INFORMATION

SHRINK RATIO - 3:1
 LONGITUDINAL SHRINKAGE ON FULL RECOVERY 0 TO-15%
 STANDARD COLOUR: BLACK
 TUBING CUT TO SPECIFIC LENGTHS CAN BE SUPPLIED FROM THE PRODUCT SIZES REFERENCED WITHIN THIS DRAWING.

STANDARD CUTTING TOLERANCES(mm)	
CUT LENGTH	TOLERANCE
UPTO TO 9.90mm	±1.50mm
10mm TO 24.90mm	±1.50mm
25mm TO 54.90mm	±1.50mm
55mm TO 99.90mm	±3.00mm
100mm TO 149.90mm	±4.00mm
150mm TO 499.90mm	±5.00mm
500mm AND GREATER	±25.40mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm(Inches)



MATERIAL
SEE NOTE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

- 0 PLC ±0.1
- 1 PLC ±0.1
- 2 PLC ±0.01
- 3 PLC ±0.001
- 4 PLC ±0.0001
- ANGLES ±
- FINISH -

DWN 16MAY2023
BASAVARAJA D A

CHK 16MAY2023
SELVAPANDIAN B

APVD 16MAY2023
MAYO BAKARF

PRODUCT SPEC
108-120009

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING



NAME
ATUM 3_TO_1 RATIO-IRRADIATED MODIFIED POLYOLEFIN DUAL WALL HEAT SHRINK TUBING

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 - ©-ATUM-175-155-0-STK -

SCALE NTS SHEET 1 OF 1 REV A