


REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	B	REVISED PER ECO-19-009164	24JUN2020	KG DR



- 1 WIRE RANGE IS FOR 6 AWG. STANDARD WIRE CROSS SECTIONAL AREA RANGE: 20,800-33,100 CMA, STRANDED WIRE
 - 2 TERMINAL BODY MATERIAL THK IS 1.448 ± 0.076 [.057 ± .003]
 - 3 RECOMMENDED OPERATING TEMP -55°C [131°F] TO $+200^{\circ}\text{C}$ [392°F] FOR HEAT SHRINK TUBING
 - 4 HEAT SHRINK TUBING SHELF LIFE OF 18 MONTHS FROM DATE CODE ON LABEL
- △ 5 TERMINAL BODY PRODUCT SPECIFICATION 108-32046 APPLICATION SPECIFICATION 114-2162

1	8-1190141-0	HIGH AND LOW TEMPERATURE CROSS LINKED FLUOROPOLYMER HEAT SHRINK TUBING 9.53 [.375]MIN ID X 25.400 ± 2.032 [1.000 ± .080] RT555-3/8-0-SP
1	323170	TERMINAL BODY: COPPER PER ASTM B152 ANNEALED FINISH: NICKEL PLATE 0.00762 [.000300] MIN EXT THK PER SAE AMS QQ-N-290
-1	PART NO	DESCRIPTION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 08DEC09	STE TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK TOM MICHIELUTTI 08DEC09		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD TOM MICHIELUTTI 08DEC09	NAME -	
0 PLC ± -		PRODUCT SPEC	HEAT RESISTANT TERMINAL KIT WIRE SIZE: 6 AWG	
1 PLC ± -		APPLICATION SPEC		
2 PLC ± -		WEIGHT	SIZE	CAGE CODE
3 PLC ± 0.127[.005]		FINISH	DRAWING NO	RESTRICTED TO
4 PLC ± -		SEE TABLE	A3	00779
ANGLES ± 1°		SEE TABLE	C-696637	
MATERIAL		CUSTOMER DRAWING	SCALE	SHEET
SEE TABLE			5:1	1 OF 1
				REV B