


© - TE Connectivity. All Rights Reserved.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER ECO-19-009164	25JUN2020	KG	DR



- 1 WIRE RANGE IS FOR 3/0 AWG. STANDARD WIRE CROSS SECTIONAL AREA RANGE: 150,500-190,000 CMA, STRANDED WIRE.
 - 2 TERMINAL BODY MATERIAL THK IS 2.311±0.0762[.091±.003].
 - 3 RECOMMENDED OPERATING TEMP -55°C [131°F] TO +200°C [392°F] FOR HEAT SHRINK TUBING
 - 4 HEAT SHRINK TUBING SHELF LIFE OF 18 MONTHS FROM DATE CODE ON LABEL
- △ 5 TERMINAL APPLICATION SPECIFICATION 114-2162

1	1-1197706-9	HIGH AND LOW TEMPERATURE CROSS LINKED FLUOROPOLYMER HEAT SHRINK TUBING 25.40[1.00] MIN IDX50.80±3.05[2.00±.12] RT555-1-0-SP
1	321874-2	TERMINAL BODY: COPPER PER ASTM B152 ANNEALED FINISH: NICKEL PLATE 0.00762 [.000300] MIN EXT THK PER SAE AMS QQ-N-290
-1	PART NO	DESCRIPTION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 08DEC09	STE TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK T MICHELUTTI 08DEC09			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD T MICHELUTTI 08DEC09	NAME		
0 PLC ± -		PRODUCT SPEC		HEAT RESISTANT TERMINAL KIT	
1 PLC ± -		APPLICATION SPEC		WIRE SIZE: 3/0 AWG	
2 PLC ± -		△ 5		SIZE	RESTRICTED TO
3 PLC ± 0.127 [.005]		WEIGHT		CAGE CODE	DRAWING NO
4 PLC ± -		-		A3	00779
ANGLES ± 1°		-		C	696652
MATERIAL	FINISH	SCALE			
SEE TABLE	SEE TABLE	3:1			
		CUSTOMER DRAWING		SHEET	REV
				1 OF 1	B