


© - TE Connectivity. All Rights Reserved.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER ECO-19-009164	25JUN2020	SJ	DR



1. WIRE RANGE IS FOR 4/0 AWG. STANDARD WIRE CROSS SECTIONAL AREA RANGE: 190,000-231,100 CMA, STRANDED WIRE
2. TERMINAL BODY MATERIAL THK IS 2.590±0.076[.102±.003]
3. RECOMMENDED OPERATING TEMP -55°C(-67°F) TO +200°C(392°F) FOR HEAT SHRINK TUBING.
4. HEAT SHRINK TUBING SHELF LIFE OF 18 MONTHS FROM DATE CODE ON LABEL.

△ 5 TERMINAL APPLICATION SPECIFICATION 114-2162

1	1-1197706-9	HIGH AND LOW TEMPERATURE CROSS LINKED FLUOROPOLYMER HEAT SHRINK TUBING 25.40[1.00] MIN ID X 50.80±3.05[2.00±.12] RT555-1-0-SP
1	321878-1	TERMINAL BODY: COPPER PER ASTM B152 ANNEALED FINISH: NICKEL PLATE 0.00762[.000300] MIN EXT THK PER SAE AMS QQ-N-290
-1	PART NO	DESCRIPTION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 10DEC09	STE TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK MJ SPICER 10DEC09			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD MJ SPICER 10DEC09	NAME		
0 PLC ± -		PRODUCT SPEC	HEAT RESISTANT TERMINAL KIT		
1 PLC ± -		APPLICATION SPEC	WIRE SIZE: 4/0 AWG		
2 PLC ± -		△ 5	SIZE	CAGE CODE	DRAWING NO
3 PLC ± 0.127 [.005]			A3	00779	C-696656
4 PLC ± -			RESTRICTED TO		
ANGLES ± 1°			-		
MATERIAL	FINISH	WEIGHT	SCALE		
SEE TABLE	SEE TABLE	-	3:1		
CUSTOMER DRAWING			SHEET	REV	
			1 OF 1	B	