


| REVISIONS | | | | | |
|-----------|-----|---------------|-----------|-----|------|
| P | LTR | DESCRIPTION | DATE | DWN | APVD |
| D3 | | ECR-24-212797 | 05JUL2024 | DC | NW |

1. MATERIALS : REFER TO TABLE.
2. A: ALL MATERIALS, COMPONENTS AND PROCESSES SHALL COMPLY WITH TEC-138-702 (CONTAINS NO BANNED OR RESTRICTED SUBSTANCES)
- B: NO REACH SVHC SHALL BE CONTAINED ABOVE THE THRESHOLD AS DEFINED IN REACH SVHC
- C: BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.

③ IDENTIFICATION INCLUDES : FOUR DIGIT DATE CODE(FIRST 2 DIGITS FOR THE WEEK CODE AND THE 2ND TWO DIGITS FOR THE YEAR CODE), MANUFACTURING CONTROL NUMBER, TE PART NUMBER & REVISION NO.



| | | | |
|------------------------|-----------|-----|-------------|
| UMCC GEN.4 (MHF4 TYPE) | 0.81 | 250 | 1-2344656-4 |
| | | 960 | 1-2344656-3 |
| | | 800 | 1-2344656-2 |
| UMCC GEN.4 (MHF4 TYPE) | 0.81 | 200 | 2344656-8 |
| | | 150 | 2344656-7 |
| | | 100 | 2344656-6 |
| | | 50 | 2344656-5 |
| UMCC GEN.1 (MHF1 TYPE) | 1.13 | 200 | 2344656-4 |
| | | 150 | 2344656-3 |
| | | 100 | 2344656-2 |
| | | 50 | 2344656-1 |
| CONNECTOR TYPE | B | A | PART NUMBER |
| | DIMENSION | | |

| | | |
|----------------------|--------------|----------|
| DOUBLE-SIDED TAPE | ADHESIVE | 3 |
| COAXIAL CABLE & CONN | CABLE ASSY | 2 |
| PI | FPCB ANTENNA | 1 |
| MATERIAL | NAME | ITEM NO. |

| | | | | | |
|--|-----|------------------|------------------------------|------------|------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN | 22OCT2018 | PAUL HUNAG | |
| DIMENSIONS: mm | | CHK | 22OCT2018 | AKU HUANG | |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: | | APVD | 22OCT2018 | AMOS CHEAH | |
| 0 PLC | ± - | PRODUCT SPEC | NAME | | |
| 1 PLC | ± - | APPLICATION SPEC | WLAN DUAL BAND ANTENNA FPC V | | |
| 2 PLC | ± - | WEIGHT | SIZE | CAGE CODE | DRAWING NO |
| 3 PLC | ± - | WEIGHT | A2 | 00779 | C=2344656 |
| 4 PLC | ± - | WEIGHT | RESTRICTED TO | | |
| ANGLES | ± - | CUSTOMER DRAWING | SCALE | SHEET | REV |
| | | | 1:1 | 1 of 2 | D3 |