





P	LTR	DESCRIPTION	DATE	DWN	APVD
P		REVISED PER ECR-24-206856	08MAY2024	DK	JP



- PINS TO COMPLY WITH AMP SOLDERABILITY SPEC. 109-11-3.
- 0.00381 MIN MATTE TIN LEAD PLATE OVER 0.00127 MIN NICKEL.
- 0.00076 MIN GOLD PLATE IN THE LOCALIZED PLATE AREA, 0.00381 MATTE TIN LEAD IN THE LOCALIZED PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.
- 0.00381 MIN MATTE TIN PLATE OVER 0.00127 MIN NICKEL.
- 0.00076 MIN GOLD PLATE IN THE LOCALIZED PLATE AREA, 0.00381 MATTE TIN IN THE LOCALIZED PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.



RECOMMENDED LAYOUT FOR 1.57 THICK BOARD
TOLERANCES NON-ACCUMULATIVE



	BRASS, GOLD	5	NYLON, UL94V-0	WHITE	1-770190-1
	BRASS, TIN	4	NYLON, UL94V-0	WHITE	1-770190-0
OBSOLETE	BRASS, GOLD	3	NYLON, UL94V-0	WHITE	-770190-2
	BRASS, TIN-LEAD	2	NYLON, UL94V-0	WHITE	770190-1
	MATERIAL	FINISH	MATERIAL	COLOR	PART NO.
	PIN		HOUSING		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	S CARPENTER	08JUN05
DIMENSIONS: mm		CHK	R JONES	6/8/05
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	R JONES	6/8/05
0 PLC	± -	PRODUCT SPEC	NAME	
1 PLC	± -	APPLICATION SPEC	TE Connectivity	
2 PLC	± 0.13		HEADER ASSEMBLY, 15 CKT, MINI UNIVERSAL MATE-N-LOK	
3 PLC	± -		SIZE	CAGE CODE
4 PLC	± -		A2	00779
ANGLES	± -	WEIGHT	DRAWING NO	
		0.000000	C=770190	
MATERIAL	FINISH	CUSTOMER DRAWING	SCALE	SHEET
			5:1	1 of 1
			REV	P