


POS-NR.	Part	Material	Quantity
1	lower part	Al alloy tinned	1
2	upper part	Al alloy tinned	1
3	bolt M8x50	stainless steel	1
4	spring washer	stainless steel	1
5	o-ring	NBR quality, 70 shore A	1

Burr Projection:		DEBUR AND BREAK SHARP EDGES		DO NOT SCALE DRAWING		REVISION: 0	
FORM BOUND MEASURE:		DIMENSION: mm		This Information is confidential and proprietary to Tyco Electronics Corporation and its subsidiaries and affiliates. It may not be disclosed to anyone, other than Tyco Electronics personnel, without written authorization from Tyco Electronics Corporation, Harrisburg, Pennsylvania USA.			
NOT FORM BOUND MEASURE:				DESCRIPTION: HEL-4812.2-KB; RPN: 116596-000 flat direct clamp 35-150 mm ² with stainless steel bolt M8x50 customer drawing			
NAME	SIGNATURE	DATE	MATERIAL:	DWG NO.		A4	
DRAWN	S.Pollakowski	09.05.2017		C-4812.2-KB M8x50			
CHK'D			SURFACE:	SCALE:		SHEET: 1 OF 1	
APPV'D			WEIGHT: 68g	1:1			
 Tyco Electronics Raychem GmbH Standort Berlin Trachenbergring 85 12247 Berlin (Germany)							