






REVISIONS					
REV	DESCRIPTION	DATE	BY	CHK	APP'D
F1	REVISED PER ECR-24-196907	17JUL2024	MV	JP	

- PINS TO COMPLY WITH AMP SOLDERABILITY SPEC. 108-11-3.
- 0.00381 MIN MATTE TIN LEAD OVER 0.00127 MIN NICKEL.
- 0.00076 MIN GOLD PLATE IN THE LOCALIZED PLATE AREA, 0.00381 MATTE TIN LEAD IN THE LOCALIZED PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.
- 0.00381 MIN MATTE TIN OVER 0.00127 MIN NICKEL.
- 0.00076 MIN GOLD PLATE IN THE LOCALIZED PLATE AREA, 0.00381 MATTE TIN IN THE LOCALIZED PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.



RECOMMENDED MOUNTING HOLE PATTERN FOR 1.57 THICK P.C. BOARD



MATERIAL	FINISH	MATERIAL	COLOR	PART NO.
BRASS, GOLD	5	NYLON, UL94V-0	WHITE	1-794068-1
BRASS, TIN	4	NYLON, UL94V-0	WHITE	1-794068-0
SUPERSEDE WITH 1-794068-1	3	NYLON, UL94V-0	WHITE	794068-2
SUPERSEDE WITH 1-794068-0	2	NYLON, UL94V-0	WHITE	794068-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN S CARPENTER 09JUN05		TE Connectivity	
DIMENSIONS: mm		CHK R JONES 29JUL2003		NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APP'D R JONES 29JUL2003		PRODUCT SPEC	
0. PLC ± -		APPLICATION SPEC		SIZE CAGE CODE DRAWING NO	
1. PLC ± -		WEIGHT		RESTRICTED TO	
2. PLC ± 0.13		A1 00779 C=794068		SCALE 5:1 SHEET 1 OF 1 REV F1	
3. PLC ± -		CUSTOMER DRAWING			
4. PLC ANGLES ± -					
MATERIAL - FINISH -					