



	Description	Material
1	hexagon screw M10x55	steel 8.8, electro galvanized
2	spring washer 23x10,5x2,5	spring steel, electro galvanized
3	upper part HEL-4843 OT	high strength AL-alloy, corrosion-resistant
4	lower part HEL-4843 UT	high strength AL-alloy, corrosion-resistant
5	o-Ring	rubber NBR 70 Shore A

Tolerances not specified according to DIN ISO 2768-1 m		BURR PROJECTION:	DEBUR AND BREAK SHARP EDGES DIMENSION: mm	DO NOT SCALE DRAWING	REVISION: 0
		FORM BOUND MEASURE:		This Information is confidential and proprietary to Tyco Electronics Corporation and its subsidiaries and affiliates. It may not be disclosed to anyone, other than Tyco Electronics personnel, without written authorization from Tyco Electronics Corporation, Harrisburg, Pennsylvania USA.	
		NOT FORM BOUND MEASURE:	DESCRIPTION: Al Flat Direct Terminal Clamp for two conductors, tin-plated 35-150 sm, 50-185 se, 35-70 rm, 35-50 re		
DRAWN T. Scholze CHK'D M. Dolling APPV'D	SIGNATURE 	DATE 04.09.2007 04.09.2007	MATERIAL: SURFACE: WEIGHT: 0,095kg	DWG NO. C-HEL-4843.1	A4 SCALE: 1:1 SHEET: 1 OF 1
 Tyco Electronics Tyco Electronics Raychem GmbH Werk Falkenberg Hellsternstr. 1 04895 Schmerkendorf (Germany)					