






2.84	.112	—	—
2.77	.109	34.67	1.365
2.29	.090	28.45	1.120
1.93	.076	25.40	1.000
1.78	.070	7.49	.295
0.76	.030	7.37	.290
0.25	.010	7.24	.285
0.20	.008	4.83	.190
0.13	.005	3.56	.140
0.10	.004	3.12	.123
MM	IN	MM	IN



CONVERSION TABLE




1. THE MATING CONNECTOR MUST BE BASED ON THE DESIGN SPECIFICATIONS ON THIS DRAWING TO ENSURE OPTIMUM MATING CONDITIONS.
2. DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED CONDITION ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.



3-DIMENSIONAL MODEL
NTS



PRELIMINARY
NOT RELEASED FOR
PRODUCTION



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

0 PLC ± —
1 PLC ± —
2 PLC ± —
3 PLC ± 0.13
4 PLC ± —
ANGLES ± —
FINISH —

DWN.
K. WHITAKER
25-APR-2000

APVD
K. COBLE

PRODUCT SPEC
—

APPLICATION SPEC
—

WEIGHT
0.000000

CUSTOMER DRAWING

TE Connectivity

HOUSING, 3 POSITION,
FAN MOTOR CONNECTOR,
UNIVERSAL MATE-N-LOK

SIZE
A1

CAGE CODE
00779

DRAWING NO.
794759

RESTRICTED TO
—

SCALE
4:1

SHEET
1

OF
1

REV
2