


RATIO 1 : 1

Recommended torque:  
100 Newton meters

| POS-NO. | DESCRIPTION                                     | QTY. |
|---------|---|------|
| 1       | Upper part, made from brass, tin-plated         | 1    |
| 2       | Lower contact part, made from brass, tin-plated | 1    |
| 3       | Threaded pin M16, made from steel, galvanized   | 1    |
| 4       | Nut, made from steel, SW24                      | 2    |
| 5       | Tension washer, made from spring steel          | 2    |
| 6       | C-lock pin, made from steel                     | 1    |

|   |           |                             |                 |  |  |                    |  |
|---|-----------|-----------------------------|-----------------|--|--|--------------------|--|
| BURR PROJECTION:  |           | DEBUR AND BREAK SHARP EDGES |                 | DO NOT SCALE DRAWING   |  | REVISION: <b>1</b> |  |
| FORM BOUND MEASURE:   |           | DIMENSION: <b>mm</b>        |                 | This Information is confidential and proprietary to Tyco Electronics Corporation and its subsidiaries and affiliates. It may not be disclosed to anyone, other than Tyco Electronics personnel, without written authorization from Tyco Electronics Corporation, Harrisburg, Pennsylvania USA. |  |                    |  |
| NOT FORM BOUND MEASURE:   |           |                             |                 | DESCRIPTION:<br><b>Flat direct terminal clamp for two conductor</b><br>HEL-4858; RPN: 107568-000<br>for conductor cross section: 2x95-300mm <sup>2</sup> RE/ RM  |  |                    |  |
| NAME  | SIGNATURE | DATE                        | MATERIAL:       | DWG NO.  |  | A4                 |  |
| DRAWN S. Pollakowski  |           | 25.03.2021                  |                 | C-HEL-4858   |  |                    |  |
| CHK'D   |           |                             |                 |  |  |                    |  |
| APPV'D  |           |                             |                 |  |  |                    |  |
| <br><b>Tyco Electronics Raychem GmbH</b><br>a TE Connectivity Ltd. company<br>Trachenbergring 85<br>12249 Berlin (Germany) |           |                             | SURFACE:        | SCALE:   |  | SHEET: 1 OF 1      |  |
|   |           |                             | WEIGHT: 0,852kg |  |  |                    |  |