






1. PARTS COMPLY TO AMP SOLDERABILITY SPECIFICATION 109-11-3.


2. CIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES, BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.

3. DIMENSIONS IN BRACKETS ARE IN INCHES.

4. DIMENSION SHOWN REPRESENT PRODUCT IN DRY CONDITION. ADDITIONAL 2% GROWTH DUE TO END USE LOCATION MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.




3 DIMENSIONAL MODEL
SCALE 4:1



RECOMMENDED MOUNTING HOLE PATTERN
FOR 1.57 [.062] THICK P.C. BOARD

PHOSPOR BRONZE, PRE-TIN PIN CONTACT MATERIAL AND FINISH	NYLON, UL94V-0, WHITE HOUSING MATERIAL AND COLOR	794932-1 PART NUMBER
--	---	-------------------------



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER CHK S. RIDGILL APVD S. RIDGILL	06-JAN-04 06-JAN-04 06-JAN-04
DIMENSIONS: mm[INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME	
	0 PLC ±"	PRODUCT SPEC	
	1 PLC ±"	APPLICATION SPEC	
	2 PLC ±0.13(.005)	WEIGHT	
3 PLC ±"	4 PLC ±"	SIZE	
ANGLES ±0°30'	FINISH	CAGE CODE	
MATERIAL SEE TABLE	SEE TABLE	DRAWING NO	
CUSTOMER DRAWING		RESTRICTED TO	



TE Connectivity

SOCKET HEADER ASSEMBLY,
5 CIRCUIT, SELECTIVELY LOADED,
UNIVERSAL MATE-N-LOK™

A100779C=794932

SCALE 5:1 SHEET 1 OF 1 REV A