


Recommended torque:
23 Newton meters

POS-NR.	DESCRIPTION	QUANTITY
1	Frame, steel hot dipped	1
2	Upper part, brass tin-plated	1
3	Screw, brass tin-plated	1
4	Tension washer, spring steel	1
5	Pressure plate	1
6	Contact part, Copper tin-plated	1

Burr Projection:		Debur and Break Sharp Edges		DO NOT SCALE DRAWING		Revision: 1	
Form Bound Measure:		Dimension: mm		This Information is confidential and proprietary to Tyco Electronics Corporation and its subsidiaries and affiliates. It may not be disclosed to anyone, other than Tyco Electronics personnel, without written authorization from Tyco Electronics Corporation, Harrisburg, Pennsylvania USA.			
Not Form Bound Measure:				Description: Steel type flat direct terminal clamp HEL-4865-TNL; RPN: 779708-000 for single flat terminals up to a wide of 25mm and with terminal plate			
NAME	SIGNATURE	DATE	DWG NO.		A4		
DRAWN S. Pollakowski		01.03.2021	C-HEL-4865-TNL				
CHK'D			SCALE:		1:1		
APPV'D			WEIGHT:		0,265kg		
 Tyco Electronics Raychem GmbH a TE Connectivity Ltd. company Trachenbergring 85 12249 Berlin (Germany)			SCALE:		1:1		
			SHEET:		1 OF 1		