


NUMBER	825435
USED FOR	E 75-9233
WAS	-

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F2	REVISED PER ECN-24-249585	01FEB2024	RK	CAS

POS.	L±0.5	PART NO
-	-	-
2	5.08	825435 -2
3	7.62	-3 ³
4	10.16	-4
5	12.70	-5 ³
6	15.24	-6 ³
7	17.78	-7
8	20.32	-8 ³
9	22.86	-9 ³
10	25.40	-10 ³
11	27.94	1- -1
12	30.48	1- -2
13	33.02	1- -3
14	35.56	1- -4 ³
15	38.10	1- -5
16	40.64	1- -6 ⁴
17	43.18	1- -7
18	45.72	1- -8
19	48.26	1- -9
20	50.80	2- -0 ³
21	53.34	2- -1 ²
22	55.88	2- -2 ³
23	58.42	2- -3
24	60.96	2- -4
25	63.50	2- -5
26	66.04	2- -6
27	68.58	2- -7 ³
28	71.12	2- -8
29	73.66	2- -9 ³
30	76.20	3- -0 ³
31	78.74	3- -1
32	81.28	3- -2
33	83.82	3- -3
34	86.36	3- -4
35	88.90	3- -5
36	91.44	3- -6
37	93.98	3- -7 ³
38	96.52	3- -8
39	99.06	3- -9
40	101.60	4- -0
41	104.14	4- -1
42	106.68	4- -2
43	109.22	4- -3
44	111.76	4- -4
45	114.30	4- -5
46	116.84	4- -6
47	119.38	4- -7
48	121.92	4- -8
49	124.46	4- -9
50	127.00	5- 825435 -0



- ① MATING SIDE: Min 0.76µm (PdNi + Au FLASH) IN ZONE "F" OVER Min 1.27µm Ni
(Alternative plating - Min 0.76µm Au OVER Min 1.27µm Ni)
SOLDER SIDE: 3-5µm TIN OVER Min 1.27µm NICKEL
- ② OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- ③ OBSOLETE

CONTACT PIN	CuZn	①
PEN HOUSING	PBT GV	GREEN
DESCRIPTION	MATERIAL	SURFACE COLOR

TE Connectivity. All Rights Reserved.

DIMENSIONS: mm	DWN	11APR1984	MATERIAL	-	FINISH	-
	CHK	11APR1984	TE Connectivity			
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2mm	APVD	-				
0 PLC ± -	PRODUCT SPEC	108-18012	NAME			
1 PLC ± -	APPLICATION SPEC	-	AMPMODU II PIN HEADER, SINGLE ROW			
2 PLC ± -	WEIGHT	-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
3 PLC ± -			A4	00779	825435	-
4 PLC ± -						
ANGLES ± -						
CUSTOMER DRAWING			SCALE	4:1	SHEET	1 OF 1
						REV F2