



P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	NEW DRAWING	14MAY2024	AN	VN



PRODUCT DIMENSIONS

SIZES	AS SUPPLIED		AS RECOVERED			
	MINIMUM EXPANDED I.D. (D)		MAXIMUM RECOVERED I.D. (d)		WALL THICKNESS AFTER RECOVERY (W)	
	mm.	in.	mm.	in.	mm.	in.
1.5/0.5	1.50	0.059	0.50	0.020	0.45±0.12	0.018±0.005
3/1	3.00	0.118	1.00	0.039	0.55±0.12	0.022±0.005
6/2	6.00	0.236	2.00	0.079	0.65±0.12	0.026±0.005
9/3	9.00	0.354	3.00	0.118	0.75±0.15	0.030±0.006
12/4	12.00	0.472	4.00	0.157	0.75±0.15	0.030±0.006
18/6	18.00	0.709	6.00	0.236	0.85±0.15	0.033±0.006
24/8	24.00	0.945	8.00	0.315	1.00±0.20	0.039±0.008
39/13	39.00	1.535	13.00	0.512	1.15±0.25	0.045±0.010


PRODUCT INFORMATION

- 1 FLAME RETARDANT
- 2 MATERIAL: IRRADIATED MODIFIED POLYOLEFIN  
STANDARD COLOURS: BLACK, WHITE, RED, BLUE, YELLOW, CLEAR  
NON-STANDARD COLOUR: BROWN, ORANGE, GREEN, VIOLET, GREY
- 3 SHRINK RATIO 3:1
- 4 LONGITUDINAL CHANGE +5% TO -10%
- 5 TUBING CUT TO SPECIFIC LENGTHS CAN BE SUPPLIED FROM THE PRODUCT SIZES REFERENCED WITHIN THIS DRAWING

STANDARD CUTTING TOLERANCES (mm)	
CUT LENGTH	TOLERANCE
UPTO TO 9.90mm	±1.50mm
10mm TO 24.90mm	±1.50mm
25mm TO 54.90mm	±1.50mm
55mm TO 99.90mm	±3.00mm
100mm TO 149.90mm	±4.00mm
150mm TO 499.90mm	±5.00mm
500mm AND GREATER	±25.40mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm



MATERIAL  
SEE NOTES

TOLERANCES UNLESS OTHERWISE SPECIFIED:  
0 PLC ±0.1  
1 PLC ±0.1  
2 PLC ±0.01  
3 PLC ±0.001  
4 PLC ±0.0001  
ANGLES ±  
FINISH -

DWN	14MAY2024
AYESHABANU N	
CHK	14MAY2024
BASAVARAJA D A	
APVD	14MAY2024
VLADIMIR NEMEC	
PRODUCT SPEC	108-120044
APPLICATION SPEC	114-120022
WEIGHT	-
CUSTOMER DRAWING	



NAME  
CGPT(3:1 Ratio)-IRRADIATED MODIFIED POLYOLEFIN SINGLE WALL HEAT SHRINK TUBING

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	-	CGPT_3-to-1-RATIO-STANDARD-SIZES	-
SCALE	SHEET	OF	REV
NTS	1	1	B