



3. CAVITY LOCATION DIMENSIONS INCREASE IN INCREMENTS OF 2.54 TOLERANCE NON-CUMULATIVE
4. USE EXTRACTION TOOL 91052-1 TO REMOVE RECEPTACLE CONTACTS.
5. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D. RENAUD/D. SINISI
6. 'TE' PART NUMBER AND DATE CODE MARKED WHEN HOUSING SIZE PERMITS.
7. 1.17±.38 CHARS. MARKED FIRST AND EVERY 5TH CAVITY, ONE SIDE.
8. MATERIAL: GLASS FILLED THERMOPLASTIC, UL 94-V0 RATED, COLOR: BLACK
9. THE PRODUCT IS IN PROCESS FOR UL RECOGNITION.
10. THE PRODUCT IS IN PROCESS FOR QUALIFICATION, AND IS NOT YET QUALIFIED.




SECTION X - X




SECTION Z-Z

ISOMETRIC VIEW



SCALE 2:1



SCALE 2:1

	3	5-87483-3	93.98	81.28	31	64	5-87483-4
OBSELETE		5-87483-1	86.36	73.66	28	58	5-87483-2
OBSELETE		4-87483-9	83.82	71.12	27	56	5-87483-0
OBSELETE		4-87483-7	76.20	63.50	24	50	4-87483-8
		4-87483-5	73.66	60.96	23	48	4-87483-6
		4-87483-3	71.12	58.42	22	46	4-87483-4
		4-87483-1	66.04	53.34	20	42	4-87483-2
		3-87483-9	60.96	48.26	18	38	4-87483-0
		3-87483-7	58.42	45.72	17	36	3-87483-8
		3-87483-5	55.88	43.18	16	34	3-87483-6
		3-87483-3	50.80	38.10	14	30	3-87483-4
		3-87483-1	48.26	35.56	13	28	3-87483-2
		2-87483-9	43.18	30.48	11	24	3-87483-0
		2-87483-7	40.64	27.94	10	22	2-87483-8
		2-87483-5	35.56	22.86	8	18	2-87483-6
		2-87483-3	30.48	17.78	6	14	2-87483-4
		2-87483-1	27.94	15.24	5	12	2-87483-2
		1-87483-9	25.40	12.70	4	10	2-87483-0
		1-87483-7	22.86	10.16	3	8	1-87483-8
		1-87483-5	20.32	7.62	2	6	1-87483-6
		1-87483-3	78.74	66.04	25	52	1-87483-4
		1-87483-1	68.58	55.88	21	44	1-87483-2
		87483-9	63.50	50.80	19	40	1-87483-0
		87483-7	53.34	40.64	15	32	87483-8
		87483-5	45.72	33.02	12	26	87483-6
		87483-3	38.10	25.40	9	20	87483-4
		87483-1	33.02	20.32	7	16	87483-2
		UNMARKED HOUSING PART NUMBER	"L" DIM	"K" DIM	NUMBER OF SPACES	NUMBER OF POSITIONS	MARKED HOUSING PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. SCHLAG BG 12-27-89		 TE Connectivity	
DIMENSIONS:		CHN P. SREMICH 10-5-93		NAME MOD IV CRIMP SNAP-IN CONNECTOR, DOUBLE ROW, 2.54 CENTERS SHORT ENTRY	
mm		APVD P. SREMICH 10-5-93			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC			
		APPLICATION SPEC			
1 P/LC ±.1 2 P/LC ±0.5 3 P/LC ±0.13 4 P/LC ±.1 ANGLES ±0° 30'		WEIGHT -		SIZE CASE CODE DRAWING NO RESTRICTED TO A 100779 C=87483 -	
MATERIAL 		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 1 REV. W3	