

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	PROPOSAL DESIGN	03AUG2018	WY	SZ
	2	REVISED	29MAY2019	WY	SZ
	A	REVISED	27JUL2020	WY	SZ

2.00

59.74

3.00

5.70

1 "TE", PART NUMBER, AND DATECODE TO BE MARKED IN AREA SHOWN. PARTS UNDER 2.00 LONG MAY BE MARKED ON BOTH SIDES.

2 MATERIAL:
HOUSING - GLASS FILLED HIGH TEMP THERMO PLASTIC, BLACK, UL94 V-0
SIGNAL CONTACT - COPPER ALLOY
POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY

3 CONTACT PLATING: NOBLE METAL PLATING ON CONTACT FUNCTIONAL AREA OF POWER AND SIGNAL CONTACTS.

4 MECHANICAL CONNECTOR KEEP OUT ZONE.

5 DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.

6 PCB - HOLE DIAMETERS ARE FINISHED HOLE SIZE.

7 PCB - .0453±.0010 DRILLED HOLES PLATED WITH .0003 MIN Sn OVER .001 TO .003 Cu PLATING TO ACHIEVE A .040 ±.003 HOLE.

54.74

45.74

5.00

28.77

2.54
5 PLC

3.00

5.50
4 PLC

23.62

14.62

14.50

3.00

57.74

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 03AUG2018

WY

CHK 03AUG2018

WY

APVD 03AUG2018

SZ

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±-
2 PLC	±0.25
3 PLC	±0.15
4 PLC	±-
ANGLES	±-

MATERIAL

- 2

FINISH

- 3

5LP + 24S + 2P

2334530-4

DESCRIPTION

PART NUMBER

TE Connectivity

NAME
RIGHT ANGLE HEADER, SOLDER
MULTI-BEAM PLUS

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2334530-4	-

CUSTOMER DRAWING

SCALE 1:1

SHEET 1 OF 2

REV A

1470-19 (3/13)

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20


REVISIONS

© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			

PART NUMBER	ROWS	LOW POWER					SIGNLA						POWER			
		LP1	LP2	LP3	LP4	LP5	1	2	3	4	5	6	P1	P2		
2334530-4	D	LM	LM	LM	LM	LM	P4	P4	P4	P4	P4	P4	TM	TN	TM	TN
	C						P3	P3	P3	P3	P4	P3				
	B						P2	P2	P2	P2	P2	P2				
	A						P1	P1	P1	P1	P1	P1				

5LP+24S+2P



STD SOLDER TYPE SIGNAL CONTACT, ROW D	P4
STD SOLDER TYPE SIGNAL CONTACT, ROW C	P3
STD SOLDER TYPE SIGNAL CONTACT, ROW B	P2
STD SOLDER TYPE SIGNAL CONTACT, ROW A	P1
STD LOWER POWER CONTACT	LM
STD SOLDER POWER CONTACT, RIGHT	TN
STD SOLDER POWER CONTACT, LEFT	TM
HOUSING	HOUSING
HOLD DOWN, MULTI-BEAM	HD
DESCRIPTION	IDENTIFIER

RECOMMENDED PCB LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±-
	1 PLC ±-
	2 PLC ±0.25
	3 PLC ±0.15
	4 PLC ±-
	ANGLES ±-
MATERIAL	FINISH

DWN WY	03AUG2018
CHK WY	03AUG2018
APVD SZ	03AUG2018
PRODUCT SPEC	-
APPLICATION SPEC	-
WEIGHT	-
CUSTOMER DRAWING	

TE Connectivity		NAME		RESTRICTED TO
		RIGHT ANGLE HEADER, SOLDER MULTI-BEAM PLUS		
SIZE	CAGE CODE	DRAWING NO	-	
A3	00779	2334530-4	-	
SCALE		SHEET	OF	REV
1:1		2	2	A